


Single color electrical schematic diagram
单色电气原理图




Installation View
安装视图

A4				 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92210P224RA5150
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

	A	B	C	D	E	F	G				
性能参数	1.	Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A			13.	Electrical life: 100000 cycles 电气寿命: 100000 cycles					
	2.	Rated current:3A/DC36V 额定电流:3A/DC36V			14.	mechanical: 500000cycles 机械寿命: 500000cycles					
	3.	Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min			15.	Operation method:Self repeating form 操作方式: 自复式					
	4.	Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ			16.	LED lamp power consumption: 20m以下 LED灯功耗: 20m以下					
	5.	Contact resistance:≤50mΩ 接触电阻 :≤50mΩ			17.	LED lamp lifespan: 40000h LED寿命: 40000h					
	6.	Pressing stroke:2.50mm ± 0.10 按压行程:2.50mm ± 0.10			18.	LED color: Red LED颜色: 红色					
	7.	Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10			19.	LED Lamp Voltage: 24V LED灯电压: 24V					
	8.	Nut assembly torque:5-14N 螺帽装配力矩:5-14N			20.	NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N					
	9.	Protection level:IP67 防护等级:IP67									
	10.	Explosion prevention level: IK10 防暴等级: IK10									
	11.	Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃									
	12.	Compression torque: ≤ 6N 按压扭力: ≤ 6N									
连接形式											
1.	Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下										
2.	Can be used with dedicated connectors: 可配专用接插件使用:										
2.1	1NO1NCswitch function wire: green (C) blue wire (NO) yellow wire (NC) 1NO1NC开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)										
2.2	2NO2NC switch function wire: green black wire C, blue black wire NO, yellow white wire NC 2NO2NC开关功能线材: 绿黑线C、蓝黑线NO、黄白线NC										
2.3	LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles LED功能线材: 红线正极 黑线负极 LED不分正负极										
A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92210P224RA5150
A2					X.XX ± 0.10		DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X ± 0.15		ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	X ± 0.25					
					ANGULAR	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
	A	B	C	D	E	F	G				

A					B					C					D					E					F					G				
材质参数																																		
10					luminous zone 发光区					PC 塑胶					1																			
9					LEDpin LED引脚					Brass 黄铜					1					Silvering 镀银														
8					Base 底座					PA46					1																			
7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金														
6					Contact material 接触材质					silver alloy 银合金					1																			
5					LED Base LED基座					PC 塑胶					1																			
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍														
3					Oring O型圈					Silica gel 硅胶					1																			
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注														


A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92210P224RA5150	
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR						
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission												



5	A4			 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:			
	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92210P224RA5150		
	A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
	A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD						
						X	± 0.25							
	REV	DATE	REVISION		DESCRIPTION	ISSUE	ANGULAR	_____	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission					
		A		B		C		D		E		F		G

	A	B	C	D	E	F	G																																																															
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM）≤30N、（0.3MM）≤40N、（0.5MM）≤50N、（0.75MM）≤60N 6.需要其他线长、线型、可以定制						1																																																															
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜						2																																																															
3	线束使用说明 1.2线：用于单色的指示灯、无开关功能 2.3线：用于双色指示灯、无开关功能 3.4线：用于三色灯的指示灯、无开关功能 4.3线：用于1N0/1N01NC开关、无指示灯功能 5.6线：用于2N0/2N02NC开关、无指示灯功能 6.5线：用于1N0/1N01NC、单色指示灯带开关功能 7.8线：用于2N0/2N02NC、单色指示灯带开关功能 8.6线：用于1N0/1N01NC、双色指示灯带开关功能 9.7线：用于1N0/1N01NC、三色或220v双色指示灯带开关功能						3																																																															
4							4																																																															
5	<table border="1" style="width:100%; border-collapse: collapse;"> <tr> <td style="width:5%;">A4</td> <td style="width:10%;"></td> <td style="width:15%;"></td> <td style="width:10%;"></td> <td rowspan="5" style="width:10%; text-align:center; vertical-align: middle;">  台 普 ROC PU </td> <td style="width:15%;">COMMON TOLERANCE</td> <td style="width:10%;">UNIT</td> <td style="width:10%;">MM</td> <td style="width:10%;">PROJECTED</td> <td style="width:10%; text-align:center;">  </td> <td style="width:20%;">PRODUCT NAME:</td> </tr> <tr> <td>A3</td> <td></td> <td></td> <td></td> <td></td> <td>DRAWN BY</td> <td>FUYUAN</td> <td>CHECKED BY</td> <td>COCO</td> <td>MODEL NO: TP92210P224RA5150</td> </tr> <tr> <td>A2</td> <td></td> <td></td> <td></td> <td></td> <td>DATE</td> <td>2019</td> <td>APPROVAL B</td> <td>ALEN</td> <td>Https: www.rocpcu.tw</td> </tr> <tr> <td>A1</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>REV</td> <td>DATE</td> <td>REVISION</td> <td>DESCRIPTION</td> <td>ISSUE</td> <td>ANGULAR</td> <td colspan="5" style="text-align:center; font-weight: bold; font-size: 1.2em;">ROC PCU TECHNOLOGY CO.,LTD</td> </tr> <tr> <td colspan="11" style="font-size: 0.8em;">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td> </tr> </table>							A4				 台 普 ROC PU	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:	A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92210P224RA5150	A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	A1										REV	DATE	REVISION	DESCRIPTION	ISSUE	ANGULAR	ROC PCU TECHNOLOGY CO.,LTD					Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission										
A4				 台 普 ROC PU	COMMON TOLERANCE	UNIT	MM	PROJECTED		PRODUCT NAME:																																																												
A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92210P224RA5150																																																												
A2						DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																												
A1																																																																						
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR	ROC PCU TECHNOLOGY CO.,LTD																																																															
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																																						
	A	B	C	D	E	F	G																																																															

22 M M系列双排单色按钮开关接线说明



接线说明:

- 1、供电电源的正极、按钮开关左边的C脚，接一起。
- 2、供电电源的负极，按钮开关右边的C脚，接一起。
- 3、设备的正极，按钮开关的左NO脚、按钮开关的LED正极，并接一起。
- 4、设备的负极，按钮开关的右NO脚、按钮开关的LED负极，并接一起

实现功能:

- 1、按钮开关按下去时: 设备正负极都通电, 按钮开关LED灯亮。
- 2、按钮开关按回去时: 设备正负极都断电, 按钮开关LED灯灭。

注: 说明图的电压为接线参考使用, 电源电压根据实际供电电压为准。

红线为正极 (火线)
黑线为负极 (零线)

A4					 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		X	± 0.25					
						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				