



A	B	C	D	E	F	G
1	性能参数					
2	1. Rated current:0.1A/DC36V 额定电流:0.1A/DC36V		13. Electrical life: 200000 cycles 电气寿命: 200000 cycles			
3	2. Insulation resistance:≥50MΩ 绝缘电阻: ≥50MΩ		14. mechanical: 1000000cycles 机械寿命: 1000000cycles			
4	3. Contact resistance:≤50mΩ 接触电阻: ≤50mΩ		15. Operation method:Unlocking 操作方式: 无锁式			
5	4. Pressing stroke:0.50mm ± 0.10 按压行程:0.50mm ± 0.10		16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N			
6	5. Contact stroke:0.50mm±0.10 接触行程:0.50mm±0.10					
7	6. welding temperature: 320 °C± 20 °C 焊接温度: 320 °C± 20 °C					
8	7. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration					
9	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N					
10	9. Protection level:IP67 防护等级:IP67					
11	10. Explosion prevention level: IK08 防暴等级: IK08					
12	11. Working environment temperature: -20 °C~+55 °C 工作环境温度: -20 °C~+55 °C					
13	12. Compression torque: ≤ 3N 按压扭力: ≤3N					
14						
15						
A4			UNIT	MM	PROJECTED	PRODUCT NAME:
A3			DRAWN BY	FUYUAN	CHECKED BY	MODEL NO: TP92228P2S
A2			DATE	2019	APPROVAL B	COCO
A1					ALEN	Https: www.rocpu.tw
REV	DATE	REVISION DESCRIPTION	ISSUE	ANGULAR	—	ROCPU TECHNOLOGY CO., LTD
						Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G				
材质参数											
1							1				
2							2				
3	6	Pin 引脚		Brass 黄铜	1						
4	5	Base 基座		PBT	1						
5	4	Arm nut 固定螺帽		Brass 黄铜	1	nickeling 镀镍					
6	3	Oring O型圈		Silica gel 硅胶	1						
7	2	Housing 外壳		SUS 不锈钢	1						
8	1	Key 按键		SUS 不锈钢	1						
9	NO 序号	Part name 部件名		Material 材料	QTY 数量	Remark 备注					
10	A4			 <b>台普</b> <b>ROCPU</b>	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
11	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92228P2S		
12	A2				DATE	2019	APPROVAL	B ALEN	Https: www.rocpu.tw		
13	A1				X.XX	± 0.10			<b>ROCPU TECHNOLOGY CO., LTD</b>		
14	REV	DATE	REVISION DESCRIPTION		X.X	± 0.15			Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission		
15			ISSUE		X	± 0.25					
16					ANGULAR	—					
	A	B			C	D	E	F			G