




A4					 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91937P224GS
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		X	± 0.25					
						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

A		B		C		D		E		F		G	
1	性能参数												
	1. Heating current: Ui: AC220V, Ith: 50mA 发热电流: Ui: AC220V, Ith: 50mA												
	2. Rated current:0.1A/DC36V 额定电流:0.1A/DC36V												
	3. Insulation resistance:≥50MΩ 绝缘电阻 :≥50MΩ												
	4. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ												
	5. Pressing stroke:0.50mm ± 0.10 按压行程:0.50mm ± 0.10												
	6. Contact stroke:0.50mm±0.10 接触行程 :0.50mm±0.10												
	7. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃												
	8. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration												
	9. Nut assembly torque:5-14N 螺帽装配力矩:5-14N												
2	10. Protection level:IP67 防护等级:IP67												
	11. Explosion prevention level: IK08 防暴等级: IK08												
	12. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃												
	13. Compression torque: ≤ 3N 按压扭力: ≤3N												
	14. Electrical life: 200000 cycles 电气寿命: 200000 cycles												
	15. mechanical: 1000000cycles 机械寿命: 1000000cycles												
	16. Operation method:Unlocking 操作方式: 无锁式												
	17. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N												
	18. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下												
	19. LED lamp lifespan: 40000h LED寿命: 40000h												
3	20. LED color: Green LED颜色: 绿色												
4													
5													

	A	B	C	D	E	F	G																																																																
1	材质参数 <table border="1"> <tr> <td></td><td></td><td></td><td></td><td></td></tr> <tr> <td></td><td></td><td></td><td></td><td></td></tr> <tr> <td>8</td><td>luminous zone 发光区</td><td>PC 塑料</td><td>1</td><td></td></tr> <tr> <td>7</td><td>Pin 引脚</td><td>Brass 黄铜</td><td>1</td><td>gold-plating 镀金</td></tr> <tr> <td>6</td><td>LEDpin LED脚</td><td>Brass 黄铜</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>5</td><td>Base 基座</td><td>PBT</td><td>1</td><td></td></tr> <tr> <td>4</td><td>Arm nut 固定螺帽</td><td>Brass 黄铜</td><td>1</td><td>nickeling 镀镍</td></tr> <tr> <td>3</td><td>Oring O型圈</td><td>Silica gel 硅胶</td><td>1</td><td></td></tr> <tr> <td>2</td><td>Housing 外壳</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>1</td><td>Key 按键</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>NO 序号</td><td>Part name 部件名</td><td>Material 材料</td><td>QTY 数量</td><td>Remark 备注</td></tr> </table>																	8	luminous zone 发光区	PC 塑料	1		7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金	6	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银	5	Base 基座	PBT	1		4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍	3	Oring O型圈	Silica gel 硅胶	1		2	Housing 外壳	SUS 不锈钢	1		1	Key 按键	SUS 不锈钢	1		NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注	1								
8	luminous zone 发光区	PC 塑料	1																																																																				
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金																																																																			
6	LEDpin LED脚	Brass 黄铜	1	Silvering 镀银																																																																			
5	Base 基座	PBT	1																																																																				
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍																																																																			
3	Oring O型圈	Silica gel 硅胶	1																																																																				
2	Housing 外壳	SUS 不锈钢	1																																																																				
1	Key 按键	SUS 不锈钢	1																																																																				
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注																																																																			
2								2																																																															
3								3																																																															
4								4																																																															
5	<table border="1"> <tr> <td>A4</td><td></td><td></td><td></td><td rowspan="5">  台普 ROCPCU </td><td colspan="2">COMMON TOLERANCE</td><td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td></tr> <tr> <td>A3</td><td></td><td></td><td></td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td colspan="3">MODEL NO: TP91937P224GS</td></tr> <tr> <td>A2</td><td></td><td></td><td></td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td colspan="3">Https: www.rocpcu.tw</td></tr> <tr> <td>A1</td><td></td><td></td><td></td><td colspan="7" rowspan="2"> ROCPCU TECHNOLOGY CO.,LTD </td></tr> <tr> <td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td></tr> <tr> <td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr> </table>							A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91937P224GS			A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw			A1				ROCPCU TECHNOLOGY CO.,LTD							REV	DATE	REVISION	DESCRIPTION	ISSUE														5
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																																												
A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91937P224GS																																																														
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																														
A1					ROCPCU TECHNOLOGY CO.,LTD																																																																		
REV	DATE	REVISION	DESCRIPTION									ISSUE																																																											
	A	B	C	D	E	F	G																																																																