




	A	B	C	D	E	F	G
1	性能参数			13. mechanical: 500000cycles 机械寿命: 500000cycles			
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A			14. Operation method:Self repeating form 操作方式: 自复式			
	2. Rated current:2A/DC36V 额定电流:2A/DC36V			15. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N			
	3. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						
	4. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						
	5. Pressing stroke:2.00mm ± 0.10 按压行程:2.00mm ± 0.10						
2	6. Contact stroke:1.10mm±0.10 接触行程 :1.10mm±0.10						
	7. Nut assembly torque:5-14N 螺帽装配力矩:5-14N						
	8. Protection level:IP67 防护等级:IP67						
	9. Explosion prevention level: IK09 防暴等级: IK09						
	10. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃						
	11. Compression torque: ≤ 3N 按压扭力: ≤3N						
3	12. Electrical life: 500000 cycles 电气寿命: 500000 cycles						
4							

A					B					C					D					E					F					G				
材质参数																																		
7					Base 底座					PA66					1					Baby blue 浅蓝色														
6					Terminal 接线柱					Brass 黄铜					1					nickeling 镀镍														
5					Contact material 接触材质					silver alloy 银合金					1																			
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍														
3					Oring O型圈					Silica gel 硅胶					1																			
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注														

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91637G2A
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission											