#### **HF Series**

# Common Mode Choke Coils(Line Filters) for AC Power Supply Closed Magnetic Circuit Core Type

TDK common mode choke coils(line filters) are used in a wide range of prevention of electromagnetic interference(EMI) and radio frequency interference(RFI) from power supply lines and for prevention of multifunctioning of products such as measuring equipment and system equipment.

#### **RATINGS**

| Item                    | Standard value                                  | Conditions                 |  |
|-------------------------|---|----------------------------|--|
| Rated voltage(V)        | 80 to 280*                                      |                            |  |
| Dielectric withstanding | 2000  | Between each winding for   |  |
| voltage(V)              | 2000  | 1 minute                   |  |
| Insulation resistance   | 100min.   | Between each winding for   |  |
| $(M\Omega)$             | TOOMIN.   | 1 minute, Edc 500V         |  |
| Temperature rise(°C)    | 45max.*   | With line resistance       |  |
| Operating temperature   | -20 to +120                                     | Including self-temperature |  |
| range(°C)               | -20 10 +120                                     | rise                       |  |
|                         | Japan Electric/Electronic Products Control Law, |                            |  |
| Safety standard         | UL, CSA and IEC conformed(The safety            |                            |  |
|                         | standard is not acquired with the unit only.)   |                            |  |

- \* Except particular items.
- Measuring equipment of inductance value: LCR meter(HP4261A, HP4263B or equivalent)

#### **FEATURES**

- · Wide range of selection.
- · High impedance at applicable frequency.
- High self-resonant frequency.

#### PRODUCT IDENTIFICATION

| UF  |     | V   |     | _ | □□□Y | $\square R \square$ | _ | 01  |
|-----|-----|-----|-----|---|------|---------------------|---|-----|
| (1) | (2) | (3) | (4) |   | (5)  | (6)                 |   | (7) |

(1)Core shape

UF: U-type core

TF: Toroidal core

HF: Square shaped closed magnetic circuit core type

Double-square shaped closed magnetic circuit core type

- (2)Dimensional code(Length×Height)
- (3)External shape code
- (4)TDK's internal code
- (5)Inductance value

Example) 602: 60µH×102=6mH

- (6)Rated current value Example) 2R5: 2.5A
- (7)Product management number

#### **SELECTION CHART**

| Series                                | Configuration | Type      | Inductance value<br>(mH)min. | Rated current (A) | Handling power*<br>L×l²(mH×A²) | Weight (g)typ. | Minimum package quantity<br>(pieces/box) |
|---------------------------------------|---------------|-----------|------------------------------|-------------------|--------------------------------|----------------|--|
| Closed magnetic circuit HF core types | HF2018R       | 1 to 33   | 0.3 to 2                     | 4.5               | 10                             | 840            |  |
|                                       | HF2022R       | 1 to 33   | 0.3 to 2                     | 4.5               | 10                             | 840            |  |
|                                       | HF2024        | 0.6 to 12 | 0.8 to 3                     | 7.6               | 10                             | 800            |  |
|                                       | HF2422        | 2.4 to 68 | 0.4 to 2.5                   | 15                | 19.5                           | 540            |  |
| 111                                   | HF core types | HF2430    | 2.4 to 68                    | 0.4 to 2.5        | 15                             | 19.5           | 400                                      |
|                                       |               | HF2826    | 1.8 to 35                    | 1 to 4            | 35                             | 28             | 480                                      |
|                                       |               | HF2836    | 1.8 to 35                    | 1 to 4            | 35                             | 30             | 400                                      |
|                                       |               | HF3545    | 4.7 to 33                    | 1.5 to 4          | 75                             | 65             | 140                                      |

<sup>\*</sup> Handling power=(Inductance value)×(Current)². It is possible to design within the range below this value. [Example] The coil for 2A can make even the inductance of 2.5mH or less a product for handling power 10.

#### **HF Series**


Common Mode Choke Coils(Line Filters) for AC Power Supply Closed Magnetic Circuit Core Type

## CLOSED MAGNETIC CIRCUIT CORE TYPE HF SERIES

#### **FEATURES**

- As closed magnetic circuit core as same as a toroidal core, even at its compact size, it offers large inductance and keeps the high impedance levels required in high frequency ranges.
- Since it uses a closed magnetic circuit core, the leakage flux is relatively small, allowing designers to improve the mounting density of their circuits.


## HF2018R(SQUARE SHAPED CLOSED MAGNETIC CIRCUIT CORE) TYPE SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM





# IMPEDANCE vs. FREQUENCY CHARACTERISTICS

TYPICAL ELECTRICAL CHARACTERISTICS



#### **ELECTRICAL CHARACTERISTICS**

| Part No.           | Inductance<br>(mH)min. | DC resistance $(\Omega)$ max. | Rated current (A)max. |
|--------------------|------------------------|-------------------------------|-----------------------|
| HF2018R-333Y0R3-01 | 33                     | 4.2                           | 0.3                   |
| HF2018R-253Y0R4-01 | 25                     | 2.9                           | 0.4                   |
| HF2018R-183Y0R5-01 | 18                     | 2                             | 0.5                   |
| HF2018R-103Y0R7-01 | 10                     | 1.1                           | 0.7                   |
| HF2018R-682Y0R8-01 | 6.8                    | 0.9                           | 0.8                   |
| HF2018R-402Y1R0-01 | 4                      | 0.5                           | 1                     |
| HF2018R-252Y1R3-01 | 2.5                    | 0.3                           | 1.3                   |
| HF2018R-202Y1R5-01 | 2                      | 0.2                           | 1.5                   |
| HF2018R-102Y2R0-01 | 1                      | 0.2                           | 2                     |

#### **APPLICABLE SAFETY STANDARD**

Electrical Appliance and Material Safety Law ("DENAN"), IEC60065, UL6500, CSA C22.2


• However, this product is not recognized by each regulations.

| HF2018R | 840pieces/box |
|---------|---------------|


#### **HF Series**

Common Mode Choke Coils(Line Filters) for AC Power Supply Closed Magnetic Circuit Core Type

## HF2022R(SQUARE SHAPED CLOSED MAGNETIC CIRCUIT CORE) TYPE SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM



# TYPICAL ELECTRICAL CHARACTERISTICS IMPEDANCE vs. FREQUENCY CHARACTERISTICS



#### **ELECTRICAL CHARACTERISTICS**

| Part No.           | Inductance | DC resistance   | Rated current |
|--------------------|------------|-----------------|---------------|
| Fait No.           | (mH)min.   | $(\Omega)$ max. | (A)max.       |
| HF2022R-333Y0R3-01 | 33         | 4.2             | 0.3           |
| HF2022R-253Y0R4-01 | 25         | 2.9             | 0.4           |
| HF2022R-183Y0R5-01 | 18         | 2               | 0.5           |
| HF2022R-103Y0R7-01 | 10         | 1.1             | 0.7           |
| HF2022R-682Y0R8-01 | 6.8        | 0.9             | 0.8           |
| HF2022R-402Y1R0-01 | 4          | 0.5             | 1             |
| HF2022R-252Y1R3-01 | 2.5        | 0.3             | 1.3           |
| HF2022R-202Y1R5-01 | 2          | 0.2             | 1.5           |
| HF2022R-102Y2R0-01 | 1          | 0.2             | 2             |

#### **APPLICABLE SAFETY STANDARD**

Electrical Appliance and Material Safety Law ("DENAN"), IEC60065, UL6500, CSA C22.2


• However, this product is not recognized by each regulations.

| HF2022R | 840pieces/box |
|---------|---------------|

#### **HF Series**

Common Mode Choke Coils(Line Filters) for AC Power Supply Closed Magnetic Circuit Core Type

## HF2024(SQUARE SHAPED CLOSED MAGNETIC CIRCUIT CORE) TYPE SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM



#### **ELECTRICAL CHARACTERISTICS**

| Part No.           | Inductance<br>(mH)min. | DC resistance $(\Omega)$ max. | Rated current (A)max. |
|--------------------|------------------------|-------------------------------|-----------------------|
| HF2024-123Y0R8-T01 | 12                     | 0.92                          | 0.8                   |
| HF2024-622Y1R0-T01 | 6.2                    | 0.5                           | 1                     |
| HF2024-242Y1R7-T01 | 2.4                    | 0.18                          | 1.7                   |
| HF2024-601Y3R0-T01 | 0.6                    | 0.06                          | 3                     |

#### **APPLICABLE SAFETY STANDARD**


Electrical Appliance and Material Safety Law ("DENAN"), CSA C22.2

• However, this product is not recognized by each regulations.

#### **PACKAGING QUANTITIES**

| HF2024 | 800pieces/box |
|--------|---------------|
|        |               |

# TYPICAL ELECTRICAL CHARACTERISTICS IMPEDANCE vs. FREQUENCY CHARACTERISTICS



#### **HF Series**


Common Mode Choke Coils(Line Filters) for AC Power Supply Closed Magnetic Circuit Core Type

## CLOSED MAGNETIC CIRCUIT CORE TYPE HF SERIES


#### **FEATURES**

- This series employs two outer magnetic path limbs design with windings on the center magnetic path limb of double-square shaped closed magnetic circuit ferrite core to reduce leakage flux.
- This filter uses the same closed magnetic circuit core as a toroidal core and therefore, even at its compact size, it offers large inductance and suppresses noise up to in high frequency ranges.

## HF2422(DOUBLE-SQUARE SHAPED CLOSED MAGNETIC CIRCUIT CORE) TYPE SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM



# TYPICAL ELECTRICAL CHARACTERISTICS IMPEDANCE vs. FREQUENCY CHARACTERISTICS



#### **ELECTRICAL CHARACTERISTICS**

| Part No.           | Inductance<br>(mH)min. | DC resistance $(\Omega)$ max. | Rated current (A)max. |
|--------------------|------------------------|-------------------------------|-----------------------|
| HF2422-683Y0R4-T01 | 68                     | 2.3                           | 0.4                   |
| HF2422-453Y0R5-T01 | 45                     | 1.65                          | 0.5                   |
| HF2422-333Y0R6-T01 | 33                     | 1.2                           | 0.6                   |
| HF2422-253Y0R8-T01 | 25                     | 0.88                          | 0.8                   |
| HF2422-203Y1R0-T01 | 20                     | 0.64                          | 1                     |
| HF2422-103Y1R2-T01 | 10                     | 0.38                          | 1.2                   |
| HF2422-452Y1R5-T01 | 4.5                    | 0.19                          | 1.5                   |
| HF2422-392Y1R8-T01 | 3.9                    | 0.15                          | 1.8                   |
| HF2422-332Y2R0-T01 | 3.3                    | 0.11                          | 2                     |
| HF2422-242Y2R5-T01 | 2.4                    | 0.09                          | 2.5                   |

#### APPLICABLE SAFETY STANDARD

Electrical Appliance and Material Safety Law ("DENAN"), IEC60065, UL6500, CSA C22.2


• However, this product is not recognized by each regulations.

| HF2422 | 540pieces/box |
|--------|---------------|
|        |               |

#### **HF Series**

Common Mode Choke Coils(Line Filters) for AC Power Supply Closed Magnetic Circuit Core Type

## HF2430(DOUBLE-SQUARE SHAPED CLOSED MAGNETIC CIRCUIT CORE) TYPE SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM






Recommended hole diameter: ø1.3 Dimensions in mm

#### Recommended hole

# TYPICAL ELECTRICAL CHARACTERISTICS IMPEDANCE vs. FREQUENCY CHARACTERISTICS



#### **ELECTRICAL CHARACTERISTICS**

| Part No.           | Inductance (mH)min. | DC resistance $(\Omega)$ max. | Rated current (A)max. |
|--------------------|---------------------|-------------------------------|-----------------------|
| HF2430-683Y0R4-T01 | 68                  | 2.3                           | 0.4                   |
| HF2430-453Y0R5-T01 | 45                  | 1.65                          | 0.5                   |
| HF2430-333Y0R6-T01 | 33                  | 1.2                           | 0.6                   |
| HF2430-253Y0R8-T01 | 25                  | 0.88                          | 0.8                   |
| HF2430-203Y1R0-T01 | 20                  | 0.64                          | 1                     |
| HF2430-103Y1R2-T01 | 10                  | 0.38                          | 1.2                   |
| HF2430-452Y1R5-T01 | 4.5                 | 0.19                          | 1.5                   |
| HF2430-392Y1R8-T01 | 3.9                 | 0.15                          | 1.8                   |
| HF2430-332Y2R0-T01 | 3.3                 | 0.11                          | 2                     |
| HF2430-242Y2R5-T01 | 2.4                 | 0.09                          | 2.5                   |

#### APPLICABLE SAFETY STANDARD

Electrical Appliance and Material Safety Law ("DENAN"), IEC60065, UL6500, CSA C22.2


• However, this product is not recognized by each regulations.

| HF2430 | 400nieces/box |
|--------|---------------|


#### **HF Series**

Common Mode Choke Coils(Line Filters) for AC Power Supply Closed Magnetic Circuit Core Type

## HF2826(DOUBLE-SQUARE SHAPED CLOSED MAGNETIC CIRCUIT CORE) TYPE SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM



# TYPICAL ELECTRICAL CHARACTERISTICS IMPEDANCE vs. FREQUENCY CHARACTERISTICS



#### **ELECTRICAL CHARACTERISTICS**

| Part No.           | Inductance | DC resistance   | Rated current |
|--------------------|------------|-----------------|---------------|
| Fait No.           | (mH)min.   | $(\Omega)$ max. | (A)max.       |
| HF2826-353Y1R0-T01 | 35         | 0.78            | 1             |
| HF2826-253Y1R2-T01 | 25         | 0.56            | 1.2           |
| HF2826-203Y1R5-T01 | 20         | 0.41            | 1.5           |
| HF2826-123Y1R8-T01 | 12         | 0.27            | 1.8           |
| HF2826-802Y2R0-T01 | 8          | 0.18            | 2             |
| HF2826-562Y2R5-T01 | 5.6        | 0.13            | 2.5           |
| HF2826-472Y2R8-T01 | 4.7        | 0.1             | 2.8           |
| HF2826-332Y3R0-T01 | 3.3        | 0.088           | 3             |
| HF2826-182Y4R0-T01 | 1.8        | 0.05            | 4             |

#### APPLICABLE SAFETY STANDARD

Electrical Appliance and Material Safety Law ("DENAN"), IEC60065, UL6500, CSA C22.2


• However, this product is not recognized by each regulations.

| HF2826 | 480pieces/box |
|--------|---------------|

#### **HF Series**

Common Mode Choke Coils(Line Filters) for AC Power Supply Closed Magnetic Circuit Core Type

## HF2836(DOUBLE-SQUARE SHAPED CLOSED MAGNETIC CIRCUIT CORE) TYPE SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM






Recommended hole diameter: ø1.3 Dimensions in mm

#### **ELECTRICAL CHARACTERISTICS**

| Inductance (mH)min. | DC resistance $(\Omega)$ max.                              | Rated current (A)max.   |
|---------------------|--|---|
| 35                  | 0.78   | 1   |
| 25                  | 0.56   | 1.2   |
| 20                  | 0.41   | 1.5   |
| 12                  | 0.27   | 1.8   |
| 8                   | 0.18   | 2   |
| 5.6                 | 0.13   | 2.5   |
| 4.7                 | 0.1  | 2.8   |
| 3.3                 | 0.088  | 3   |
| 1.8                 | 0.05   | 4   |
|                     | (mH)min.<br>35<br>25<br>20<br>12<br>8<br>5.6<br>4.7<br>3.3 | (mH)min. (Ω)max.  35 0.78 25 0.56 20 0.41 12 0.27 8 0.18 5.6 0.13 4.7 0.1 3.3 0.088 |

# TYPICAL ELECTRICAL CHARACTERISTICS IMPEDANCE vs. FREQUENCY CHARACTERISTICS



#### **APPLICABLE SAFETY STANDARD**

Electrical Appliance and Material Safety Law ("DENAN"), IEC60065, UL6500, CSA C22.2


• However, this product is not recognized by each regulations.

| HF2836 | 400pieces/box |
|--------|---------------|

#### **HF Series**

Common Mode Choke Coils(Line Filters) for AC Power Supply Closed Magnetic Circuit Core Type


## HF3545(DOUBLE-SQUARE SHAPED CLOSED MAGNETIC CIRCUIT CORE) TYPE SHAPES AND DIMENSIONS/CIRCUIT DIAGRAM





Recommended hole diameter: ø1.3 Dimensions in mm

# TYPICAL ELECTRICAL CHARACTERISTICS IMPEDANCE vs. FREQUENCY CHARACTERISTICS



#### **ELECTRICAL CHARACTERISTICS**

| Part No.           | Inductance | DC resistance   | Rated current |
|--------------------|------------|-----------------|---------------|
| Fait No.           | (mH)min.   | $(\Omega)$ max. | (A)max.       |
| HF3545-333Y1R5-T01 | 33         | 0.42            | 1.5           |
| HF3545-183Y2R0-T01 | 18         | 0.23            | 2             |
| HF3545-123Y2R5-T01 | 12         | 0.17            | 2.5           |
| HF3545-103Y2R7-T01 | 10         | 0.13            | 2.7           |
| HF3545-822Y3R0-T01 | 8.2        | 0.105           | 3             |
| HF3545-562Y3R5-T01 | 5.6        | 0.077           | 3.5           |
| HF3545-472Y4R0-T01 | 4.7        | 0.062           | 4             |

#### APPLICABLE SAFETY STANDARD

Electrical Appliance and Material Safety Law ("DENAN"), IEC60065, UL6500, CSA C22.2

• However, this product is not recognized by each regulations.

| HF3545 | 140pieces/box |
|--------|---------------|