

**GENNUM**  
CORPORATION


# GX4201 Wideband, Monolithic 1x1 Video Crosspoint Switch

## DATA SHEET

### FEATURES

- -3 dB bandwidth, 300 MHz with  $C_L = 0 \text{ pF}$
- off isolation at 100 MHz, 80 dB
- differential phase and gain at 4.43 MHz, 0.01° & 0.02%
- 800  $\mu\text{W}$  disabled power consumption
- input signal levels from -2 V to +3 V
- logic input compatible with TTL and 5 V CMOS
- open collector TALLY output

### FUNCTIONAL BLOCK DIAGRAM



### TRUTH TABLE

EN	OUT	TALLY
0	HIGH Z	OFF
1	IN	ON

### ABSOLUTE MAXIMUM RATINGS

Parameter	Value
Supply Voltage	$\pm 7.5 \text{ V}$
Operating Temperature Range	$0^\circ \text{ C} \leq T_A \leq 70^\circ \text{ C}$
Storage Temperature Range	$-65^\circ \text{ C} \leq T_S \leq 150^\circ \text{ C}$
Lead Temperature (Soldering, 10 Sec)	260°C
Analog Input Voltage	$-5.5 \text{ V} \leq V_{IN} \leq 5.5 \text{ V}$
Logic Input Voltage	$-0.5 \text{ V} \leq V_L \leq 5.5 \text{ V}$
Output Load Current	12mA
High Level TALLY Output Current	2 mA

### CIRCUIT DESCRIPTION

The GX4201 is a wideband 1x1 video crosspoint implemented in bipolar monolithic technology. The device is characterized by excellent differential gain and phase in the enabled state, and very high off-isolation in the disabled state. The fully buffered unilateral signal path ensures negligible output to input feedback while delivering minimal output switching transients through make-before-break switching.

For use in NxM routing matrices, the device features a very high, nearly constant input impedance, coupled with very high output impedance in the disabled state. This allows multiple GX4201's to be paralleled at the input and output without additional circuitry. An open collector PNP to  $V_{CC}$  TALLY output provides indication of crosspoint selection.

To maximize system bandwidth, an external current source is used to bias the output device of the crosspoint. One external current source is required per output bus. For less demanding applications, a load resistor can be used in place of the output current source, causing a slight increase in differential phase. Non-additive mixing will occur on the output bus if more than one paralleled GX4201 is enabled at a time.


The GX4201 is one of a series of wideband video crosspoints utilizing Gennum's proprietary LSI process.

### APPLICATIONS

- very high quality video switching
- HDTV
- computer graphics
- RF switching/routing
- PCM/data routing

### PIN CONNECTIONS

#### TOP VIEW



**ELECTRICAL CHARACTERISTICS** ( $V_S = \pm 5V$  DC,  $0^\circ C < T_A < 70^\circ C$ ,  $I_L = 6$  mA)

	PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
DC SUPPLY	Supply Voltage	$\pm V_S$		$\pm 4.5$	$\pm 5$	$\pm 5.5$	V
	Supply Current (not including external current load)	I+	EN=1	-	13.5	17	mA
			EN=0	-	80	140	$\mu A$
		I-	EN=1	-	12.5	16	mA
			EN=0	-	80	140	$\mu A$
STATIC	Analog Output Voltage Swing	$V_{OUT}$	Extremes before clipping occurs	-2	-	3	V
	Analog Input Bias Current	$I_{BIAS}$		-	12	-	$\mu A$
	Output Offset Voltage	$V_{OS}$	$T_A = 25^\circ C$	-10	-	10	mV
LOGIC	Output Offset Voltage Drift-	$\Delta V_{OS} / \Delta T$		-	-25	-80	$\mu V/C$
	Crosspoint Turn-On Time	$t_{ON}$	Control input to appearance of signal at output.	-	200	400	ns
	Crosspoint Turn-Off Time	$t_{OFF}$	Control input to disappearance of signal at output.	0.5	1.0	-	$\mu s$
	Logic Input Thresholds	$V_{IH}$	1	2.0	-	-	V
		$V_{IL}$	0	-	-	0.8	V
	Enable Bias Current	$I_{BIAS(EN)}$	EN = 0	-	0.3	2	$\mu A$
	TALLY Output	$V_{OH}$	EN = 1, $I_O = 1$ mA	4.80	4.89	4.93	V
DYNAMIC	Insertion Loss	I.L.	1V p-p sine or sq.wave, $T_A = 25^\circ C$ at 100 kHz $R_L = 100$ k $\Omega$ , $C_L = 30$ pF	0.015	0.025	0.040	dB
	Bandwidth (-3dB) See Fig. 1	B.W.	small signal $C_L = 0$ pF	-	300	-	MHz
	Input Resistance	$R_{IN}$	EN = 1	1.0	3.0	-	M $\Omega$
	Input Capacitance	$C_{IN}$	EN = 0	-	1.1	-	pF
	Output Resistance	$R_{OUT}$	EN = 1	-	7	-	$\Omega$
	Output Capacitance See Fig. 5	$C_{OUT}$	EN = 0	-	1.1	-	pF
	Differential Gain	dg	at 3.58 MHz $V_{IN} = 40$ IRE	-	-	0.04	%
	Differential Phase See Fig. 6	dp		-	-	0.04	degrees
	Off Isolation See Fig. 4		Enabled GX4201 on output $f = 100$ MHz $V_{IN} = 1$ V p-p	-	80	-	dB
	Slew Rate	+SR	$V_{IN} = 3$ V p-p ( $C_L = 0$ pF)	250	400	-	$V/\mu s$

**ORDERING INFORMATION**

PART NUMBER	PACKAGE TYPE	TEMPERATURE RANGE
GX4201-CKA	8 PIN SOIC	0° to 70°C
GX4201-CDA	8 PIN DIP	0° to 70°C
GX4201-CTA	8 PIN SOIC TAPE	0° to 70°C

### TYPICAL PERFORMANCE CURVES OF THE GX4201

For all graphs,  $V_S = \pm 5$  V DC and  $T_A = 25^\circ\text{C}$ . The curves shown below represent typical batch sampled results.




Fig. 1 Gain vs Frequency




Fig. 2 Phase vs Frequency




Fig. 3 Gain vs Frequency




Fig. 4 Off Isolation vs Frequency

continued over




Fig. 5  $C_{IN}$  vs Frequency




Fig. 6  $C_{OUT}$  vs Bias




Fig. 7  $dg/dp$  vs Input Bias




Fig. 8  $dg/dp$  vs Frequency




Fig. 9  $dg/dp$  vs  $R_L$




Fig. 10 Burn-in Test Circuit




Fig. 11a Switching Transient Test Circuit





Fig. 11b Switching Transient




NOTE: Off-isolation can be increased by eliminating the signal path through the power supplies. This is demonstrated by replacing the enabled crosspoint with a  $10\Omega$  load resistor as shown in the passive load circuit.

Active Load

Passive Load

Fig. 12 Off-isolation Test Circuits


All capacitors in farads, all resistors in ohms unless otherwise stated.



All capacitors in  $\mu\text{F}$ , all resistors in  $\Omega$  unless otherwise shown.

Fig. 13 Application Circuit  
2 x 2 Matrix using Four GX4201

- NOTES:
- \* All decoupling capacitors are  $0.1 \mu\text{F}$ , 50 V.
  - 6mA can be implemented by the following circuit. Choose a transistor with  $\beta / f_T$  at 6 mA  $f_T \geq 800\text{MHz}$ .
  - Alternatively, an  $820\Omega$  resistor may be used. The insertion loss will be increased to 0.1 dB.



## AVAILABLE PACKAGING

8 pin DIP                  8 pin SOIC  
8 pin SOIC - TAPE

**CAUTION**  
ELECTROSTATIC  
SENSITIVE DEVICES  
DO NOT OPEN PACKAGES OR HANDLE  
EXCEPT AT A STATIC-FREE WORKSTATION

## DOCUMENT IDENTIFICATION

### PRODUCT PROPOSAL

This data has been compiled for market investigation purposes only, and does not constitute an offer for sale.

### ADVANCE INFORMATION NOTE

This product is in development phase and specifications are subject to change without notice. Gennum reserves the right to remove the product at any time. Listing the product does not constitute an offer for sale.

### PRELIMINARY DATA SHEET

The product is in a preproduction phase and specifications are subject to change without notice.

### DATA SHEET

The product is in production. Gennum reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible.

Gennum Corporation assumes no responsibility for the use of any circuits described herein and makes no representations that they are free from patent infringement.

© Copyright AUG.1989 Gennum Corporation. Revision Date: January 1993. All rights reserved. Printed in Canada.