




	A	B	C	D	E	F	G
1	性能参数			12. Compression torque: ≤ 4N 按压扭力: ≤4N			
	1. Heating current: Ui: AC250V, Ith: 20A 发热电流: Ui: AC250V, Ith: 20A			13. Electrical life: 30000 cycles 电气寿命: 30000 cycles			
	2. Rated current:16A/AC110V/220V 16A/DC12V/24V 额定电流:16A/AC110V/220V 16A/DC12V/24V			14. mechanical: 200000cycles 机械寿命: 200000cycles			
	3. Power-frequency withstand voltage:1500V1min 工频耐压:1500V1min			15. Operation method:Self-locking 操作方式: 自锁式			
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ			16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N			
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						
	6. Pressing stroke:3.50mm ± 0.10 按压行程:3.50mm ± 0.10						
	7. Contact stroke:1.35mm±0.10 接触行程 :1.35mm±0.10						
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N						
	9. Protection level:IP67 防护等级:IP67						
2	10. Explosion prevention level: IK10 防暴等级: IK10						
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃						
	连接形式						
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下						
	2. Can be used with dedicated connectors: 可配专用接插件使用:						
	2.1 Switch function wire: blue wire NO (1²mm) 开关功能线材: 蓝线NO (1²mm)						
3							
4							
5							

	A	B	C	D	E	F	G																																																																	
1	材质参数 <table border="1"> <tr> <td></td><td></td><td></td><td></td><td></td></tr> <tr> <td></td><td></td><td></td><td></td><td></td></tr> <tr> <td>8</td><td>Base 底座</td><td>PBT</td><td>1</td><td></td></tr> <tr> <td>7</td><td>Pin 引脚</td><td>Brass 黄铜</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>6</td><td>Contact material 接触材质</td><td>silver alloy 银合金</td><td>1</td><td></td></tr> <tr> <td>5</td><td>Bush 衬套</td><td>PBT</td><td>1</td><td></td></tr> <tr> <td>4</td><td>Arm nut 固定螺帽</td><td>Brass 黄铜</td><td>1</td><td>nickeling 镀镍</td></tr> <tr> <td>3</td><td>Oring O型圈</td><td>Silica gel 硅胶</td><td>1</td><td></td></tr> <tr> <td>2</td><td>Housing 外壳</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>1</td><td>Key 按键</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>NO 序号</td><td>Part name 部件名</td><td>Material 材料</td><td>QTY 数量</td><td>Remark 备注</td></tr> </table>																	8	Base 底座	PBT	1		7	Pin 引脚	Brass 黄铜	1	Silvering 镀银	6	Contact material 接触材质	silver alloy 银合金	1		5	Bush 衬套	PBT	1		4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍	3	Oring O型圈	Silica gel 硅胶	1		2	Housing 外壳	SUS 不锈钢	1		1	Key 按键	SUS 不锈钢	1		NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注	1									
8	Base 底座	PBT	1																																																																					
7	Pin 引脚	Brass 黄铜	1	Silvering 镀银																																																																				
6	Contact material 接触材质	silver alloy 银合金	1																																																																					
5	Bush 衬套	PBT	1																																																																					
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍																																																																				
3	Oring O型圈	Silica gel 硅胶	1																																																																					
2	Housing 外壳	SUS 不锈钢	1																																																																					
1	Key 按键	SUS 不锈钢	1																																																																					
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注																																																																				
2								2																																																																
3								3																																																																
4								4																																																																
5	<table border="1"> <tr> <td>A4</td><td></td><td></td><td></td><td rowspan="5">  台普 ROCPCU </td> <td colspan="2">COMMON TOLERANCE</td> <td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td></tr> <tr> <td>A3</td><td></td><td></td><td></td> <td></td><td></td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td>MODEL NO: TP992506G1S</td></tr> <tr> <td>A2</td><td></td><td></td><td></td> <td>X.XX</td><td>± 0.10</td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td>Https: www.rocpcu.tw</td></tr> <tr> <td>A1</td><td></td><td></td><td></td> <td>X.X</td><td>± 0.15</td><td colspan="5" rowspan="2"> ROCPCU TECHNOLOGY CO.,LTD </td></tr> <tr> <td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td> <td>X</td><td>± 0.25</td></tr> <tr> <td></td><td></td><td></td><td></td><td></td> <td>ANGULAR</td><td>—</td><td colspan="5">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td></tr> </table>							A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP992506G1S	A2				X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	A1				X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD					REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					5
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																																													
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP992506G1S																																																													
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																													
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD																																																																	
REV	DATE	REVISION	DESCRIPTION		ISSUE	X						± 0.25																																																												
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																																	
	A	B	C	D	E	F	G																																																																	