

OF Type Crystal Oscillator

Package Size 1.6x 1.2mm

Frequency 1MHz to 54MHz

STARWAVE



FEATURE


- Typical 1.65 x 1.25 x 0.8mm ceramic SMD package-
- Operation supply voltage: 1.8V, 2.5V and 3.3V
- Tri-State Enable/Disable
- Frequency Stability ± 30 ppm over -40°C to 105°C
- Pb-free/RoHS compliant

TYPICAL APPLICATION

- Wearable device
- Mobile device
- IoT, Smartphone
- Game console

DIMENSION (mm)

SOLDER PAD LAYOUT (mm)



ELECTRICAL SPECIFICATION

Parameter	3.3V		2.5V		1.8V		Unit
	Min.	Max.	Min.	Max.	Min.	Max.	
Supply Voltage Variation	$V_{DD}-5\%$	$V_{DD}+5\%$	$V_{DD}-5\%$	$V_{DD}+5\%$	$V_{DD}-5\%$	$V_{DD}+5\%$	V
Frequency Range	1	54	1	54	1	54	MHz
Supply Current (@15pf Loading)	-	10	-	10	-	10	mA
Output Level	Output High	$90\%V_{DD}$	-	$90\%V_{DD}$	-	$90\%V_{DD}$	V
	Output Low	-	$10\%V_{DD}$	-	$10\%V_{DD}$	-	$10\%V_{DD}$
Transition Time	Rise Time / Fall Time		-	5	-	5	nSec
Duty Cycle	45	55	45	55	45	55	%
Startup Time	-	8	-	8	-	8	mSec
Tri-State	Output Enable	$0.7 \times V_{DD}$	-	$0.7 \times V_{DD}$	-	$0.7 \times V_{DD}$	V
	Output Disable	-	$0.3 \times V_{DD}$	-	$0.3 \times V_{DD}$	-	$0.3 \times V_{DD}$
Stand by Current (@PD Mode)	-	400	-	400	-	400	uA
Stand by Current (@OE Mode)	-	10	-	10	-	10	mA
Output Loading	15		15		15		pf
RMS Phase Jitter (12KHz to 20MHz)	-	0.7	-	0.7	-	0.7	pSec
Aging (@ 25°C, First Year)	-	± 3	-	± 3	-	± 3	ppm
Storage Temp. Range	-55	+125	-55	+125	-55	+125	$^{\circ}\text{C}$

Standard frequencies are frequencies which the crystal has been designed and does not imply a stock position.

+ Transition times are measured between 10% and 90% of VDD, with an output load of 15pF.

FREQ. STABILITY vs. TEMP. RANGE

Temp. ppm (°C)	±15	± 20	±25	±50
-20~+70	△	○	○	○
-40~+85	×	△	○	○
-40~+105	×	×	×	△

*O: Available △: Conditional X: Not available

*Inclusive of calibration @ 25 °C ,operating temperature range, i Voltage variation,load variation,aging (1st year),shock,and vibrati

Note: not all combination of options are available. Other specifications may be available upon request.

OF Type Crystal Oscillator

Package Size 1.6x 1.2mm

Frequency 1MHz to 54MHz



Ordering Information




Table 13. Ordering Codes for Supported Tape & Reel Packing Method

Device Size (mm x mm)	16 mm T&R (3ku)	16 mm T&R (1ku)	12 mm T&R (3ku)	12 mm T&R (1ku)	8 mm T&R (3ku)	8 mm T&R (1ku)
1.6 x 1.2	-	-	-	-	D	E
2.0 x 1.6	-	-	-	-	D	E
2.5 x 2.0	-	-	-	-	D	E
3.2 x 2.5	-	-	-	-	D	E
5.0 x 3.2	-	-	T	Y	-	-
7.0 x 5.0	T	Y	-	-	-	-