




A4						COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP992504P1S
A2						X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1						X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE		X	± 0.25					
						ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				

A		B		C		D		E		F		G		
1	性能参数													
	1. Heating current: Ui: AC250V, Ith: 20A 发热电流: Ui: AC250V, Ith: 20A													
	2. Rated current:16A/AC110V/220V 16A/DC12V/24V 额定电流:16A/AC110V/220V 16A/DC12V/24V													
	3. Power-frequency withstand voltage:1500V1min 工频耐压:1500V1min													
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ													
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ													
	6. Pressing stroke:3.50mm ± 0.10 按压行程:3.50mm ± 0.10													
	7. Contact stroke:1.35mm±0.10 接触行程 :1.35mm±0.10													
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N													
	9. Protection level:IP67 防护等级:IP67													
2	10. Explosion prevention level: IK10 防暴等级: IK10													
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃													
	12. Compression torque: ≤ 4N 按压扭力: ≤4N													
	13. Electrical life: 30000 cycles 电气寿命: 30000 cycles													
	14. mechanical: 200000cycles 机械寿命: 200000cycles													
	15. Operation method:Self-locking 操作方式: 自锁式													
	16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N													
3														
4	连接形式													
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下													
	2. Can be used with dedicated connectors: 可配专用接插件使用:													
	2.1 Switch function wire: blue wire NO (1²mm) 开关功能线材: 蓝线NO (1²mm)													
5	A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
	A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP992504P1S		
	A2							DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
	A1							ROCPCU TECHNOLOGY CO.,LTD						
	REV	DATE	REVISION	DESCRIPTION										ISSUE
	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													
	A		B		C		D		E		F		G	

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G																																																																	
1	材质参数 <table border="1"> <tr> <td></td><td></td><td></td><td></td><td></td></tr> <tr> <td></td><td></td><td></td><td></td><td></td></tr> <tr> <td>8</td><td>Base 底座</td><td>PBT</td><td>1</td><td></td></tr> <tr> <td>7</td><td>Pin 引脚</td><td>Brass 黄铜</td><td>1</td><td>Silvering 镀银</td></tr> <tr> <td>6</td><td>Contact material 接触材质</td><td>silver alloy 银合金</td><td>1</td><td></td></tr> <tr> <td>5</td><td>Bush 衬套</td><td>PBT</td><td>1</td><td></td></tr> <tr> <td>4</td><td>Arm nut 固定螺帽</td><td>Brass 黄铜</td><td>1</td><td>nickeling 镀镍</td></tr> <tr> <td>3</td><td>Oring O型圈</td><td>Silica gel 硅胶</td><td>1</td><td></td></tr> <tr> <td>2</td><td>Housing 外壳</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>1</td><td>Key 按键</td><td>SUS 不锈钢</td><td>1</td><td></td></tr> <tr> <td>NO 序号</td><td>Part name 部件名</td><td>Material 材料</td><td>QTY 数量</td><td>Remark 备注</td></tr> </table>																	8	Base 底座	PBT	1		7	Pin 引脚	Brass 黄铜	1	Silvering 镀银	6	Contact material 接触材质	silver alloy 银合金	1		5	Bush 衬套	PBT	1		4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍	3	Oring O型圈	Silica gel 硅胶	1		2	Housing 外壳	SUS 不锈钢	1		1	Key 按键	SUS 不锈钢	1		NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注	1									
8	Base 底座	PBT	1																																																																					
7	Pin 引脚	Brass 黄铜	1	Silvering 镀银																																																																				
6	Contact material 接触材质	silver alloy 银合金	1																																																																					
5	Bush 衬套	PBT	1																																																																					
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍																																																																				
3	Oring O型圈	Silica gel 硅胶	1																																																																					
2	Housing 外壳	SUS 不锈钢	1																																																																					
1	Key 按键	SUS 不锈钢	1																																																																					
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注																																																																				
2								2																																																																
3								3																																																																
4								4																																																																
5	<table border="1"> <tr> <td>A4</td><td></td><td></td><td></td><td rowspan="5">  台普 ROCPCU </td> <td colspan="2">COMMON TOLERANCE</td> <td>UNIT</td><td>MM</td><td>PROJECTED</td><td></td><td>PRODUCT NAME:</td> </tr> <tr> <td>A3</td><td></td><td></td><td></td> <td></td><td></td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td>MODEL NO: TP992504P1S</td> </tr> <tr> <td>A2</td><td></td><td></td><td></td> <td>X.XX</td><td>± 0.10</td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td>Https: www.rocpcu.tw</td> </tr> <tr> <td>A1</td><td></td><td></td><td></td> <td>X.X</td><td>± 0.15</td><td colspan="5" rowspan="2"> ROCPCU TECHNOLOGY CO.,LTD </td> </tr> <tr> <td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td> <td>X</td><td>± 0.25</td> </tr> <tr> <td></td><td></td><td></td><td></td><td></td><td>ANGULAR</td><td>—</td><td colspan="5">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td> </tr> </table>							A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP992504P1S	A2				X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	A1				X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD					REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25						ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					5
A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																																													
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP992504P1S																																																													
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																																													
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD																																																																	
REV	DATE	REVISION	DESCRIPTION		ISSUE	X						± 0.25																																																												
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																																	
	A	B	C	D	E	F	G																																																																	