





A				B				C				D				E				F				G			
1	性能参数																										
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A										13. mechanical: 500000cycles 机械寿命: 500000cycles																
	2. Rated current:3A/DC36V 额定电流:3A/DC36V										14. Operation method:Self repeating form 操作方式: 自复式																
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min										15. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N																
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ																										
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ																										
	6. Pressing stroke:2.50mm ± 0.10 按压行程:2.50mm ± 0.10																										
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10																										
	8. Protection level:IP67 防护等级:IP67																										
	9. Explosion prevention level: IK10 防暴等级: IK10																										
2																											
3																											
4	连接形式																										
	1. Welding temperature of wire: 320 ± 20 °C 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下																										
	2. Can be used with dedicated connectors: 可配专用接插件使用:																										
	2.1 Switch function wire: green (C) blue wire (NO) yellow wire (NC) 开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)																										
	2.2 LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles LED功能线材: 红线正极 黑线负极 LED不分正负极																										
5																											

A4					COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92201P2A5150B																
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw																		
A1					ROC PU TECHNOLOGY CO.,LTD																						
REV	DATE	REVISION	DESCRIPTION									ISSUE	ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission												
A				B				C				D				E				F				G			


A					B					C					D					E					F					G				
材质参数																																		
8					Base 底座					PA46					1																			
7					Pin 引脚					Brass 黄铜					1					gold-plating 镀金														
6					Contact material 接触材质					silver alloy 银合金					1																			
5					LED Base LED基座					PC 塑胶					1																			
4					Arm nut 固定螺帽					Brass 黄铜					1					nickeling 镀镍														
3					Oring O型圈					Silica gel 硅胶					1																			
2					Housing 外壳					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
1					Key 按键					Aluminum alloy 铝合金					1					Oxidized/Black 氧化/黑色														
NO 序号					Part name 部件名					Material 材料					QTY 数量					Remark 备注														

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92201P2A5150B
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					



	A	B	C	D	E	F	G																																	
1	性能参数 1.L1-导线长度：默认150MM长； 2.L2-线头长度：默认10MM 3.L3-剥头长度：默认3MM 4.S-导线导体横截面积：默认0.5平方MM、可选0.3平方MM 5.线型拉力N：（0.15-0.25MM）≤30N、（0.3MM）≤40N、（0.5MM）≤50N、（0.75MM）≤60N 6.需要其他线长、线型、可以定制																																							
2	材质参数 1.插壳：浅蓝色尼龙胶壳 2.端子：磷铜y镀锡色 3.导电线材：紫铜																																							
3	线束使用说明 1.2线：用于单色的指示灯、无开关功能 2.3线：用于双色指示灯、无开关功能 3.4线：用于三色灯的指示灯、无开关功能 4.3线：用于1NO/1NO1NC开关、无指示灯功能 5.6线：用于2NO/2NO2NC开关、无指示灯功能 6.5线：用于1NO/1NO1NC、单色指示灯带开关功能 7.8线：用于2NO/2NO2NC、单色指示灯带开关功能 8.6线：用于1NO/1NO1NC、双色指示灯带开关功能 9.7线：用于1NO/1NO1NC、三色或220v双色指示灯带开关功能																																							
5	A4				 台普 ROC CPU		<table border="1"> <tr> <td colspan="2">COMMON TOLERANCE</td> <td>UNIT</td> <td>MM</td> <td>PROJECTED</td> <td></td> <td>PRODUCT NAME:</td> </tr> <tr> <td>A3</td> <td></td> <td>DRAWN BY</td> <td>FUYUAN</td> <td>CHECKED BY</td> <td>COCO</td> <td>MODEL NO: TP92201P2A5150B</td> </tr> <tr> <td>A2</td> <td></td> <td>DATE</td> <td>2019</td> <td>APPROVAL B</td> <td>ALEN</td> <td>Https: www.rocpcu.tw</td> </tr> <tr> <td>A1</td> <td></td> <td colspan="5" rowspan="2"> ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission </td> </tr> <tr> <td>REV</td> <td>DATE</td> <td>REVISION</td> <td>DESCRIPTION</td> <td>ISSUE</td> </tr> </table>	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	A3		DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92201P2A5150B	A2		DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	A1		ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission					REV	DATE	REVISION	DESCRIPTION	ISSUE
COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:																																		
A3		DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92201P2A5150B																																		
A2		DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw																																		
A1		ROCPCU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission																																						
REV	DATE						REVISION	DESCRIPTION	ISSUE																															
	A	B	C	D	E	F	G																																	

22MM系列单排无灯按钮开关接线说明



接线说明:

- 1、供电电源的负极、设备的负极，并接一起。
- 2、供电电源的正极，按钮开关的C脚，并接一起。
- 3、设备的正极，按钮开关的NO脚，并接一起。

实现功能:

- 1、按钮开关**按下去**时：设备**通电**。
- 2、按钮开关**按回去**时：设备**断电**。

注：说明图的电压为接线参考使用，电源电压根据实际供电电压为准。

红线为正极（火线）
黑线为负极（零线）

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				