



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING:PP RESIN BLACK

b.CONTACT:BRASS

(SURFACE PLATING: NI-PLATING)

SEE ORDERING INFORMATION

2.ELECTRIC:

a.DIELECTRIC VOLTAGE: 500V AC ONE SEC LEVEL

b.OPERATING TEMPERATURE: -10°C~ +100°C

ORDERING INFORMATION

BH-AAA-A1AJ002

电池盒

电池型号

DIP 90° TYPE

PLATING:

A-Au1U"

J-Ni PLATING

K-Sn PLATING

MATERIAL:

1A-PP BLACK

1B-PA66 BLACK

2A-PPA BROWN

2B-PPA BLACK

3A-PPS BROWN

3B-PPS BLACK

4A-LCP WHITE



4B-LCP BLACK

5A-PA9T BLACK


工程部

2019-05-11

H. WANG



PCB Layout Diagram
Top View



3D View

3	SPRING	2	65C SPRING WIRE, $\phi 0.65\text{MM}$	Ni-Plating
2	PC PINS	2	BRASS, $\phi 0.8\text{MM}$	Ni-Plating
1	HOUSING	1	PP Resin	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyoungdz.com			
DECIMALS:	ANGLES:	DSND	YangFeng	DATE	2019-05-11
X : ± 0.30	X : $\pm 1^\circ$	CHKD	ZhouRuicai	DATE	2019-05-11
X.X : ± 0.25	X.X : $\pm 0.5^\circ$	APVD	XueShunyang	DATE	2019-05-11
X.XX : ± 0.20		WEIGHT:	SCALE:	SIZE: A4	VIEW:
X.XXX : ± 0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/1	OBJECT: MY
		TITLE:		PART NO.:	
		电池盒BH-AAA-2J Ni DIP插针		BH-AAA-A1AJ002	
		DRAW NO.:WD-CP-0050			