

Features

- Zero Reverse Recovery Current
- Positive Temperature Coefficient
- High-Speed Switching
- Epoxy Meets UL 94 V-0 Flammability Rating
- Halogen Free. "Green" Device (Note 1)
- Lead Free Finish/RoHS Compliant(Note 1) ("P" Suffix designates RoHS Compliant. See ordering information)

Benefits

- Temperature-Independent Performance
- Low Switching Loss
- Low Heat Dissipation Requirements

Applications

- Switching Power Supply
- Power Factor Correction
- Motor Drive, Traction
- Charging Pile

Maximum Ratings

- Operating Junction Temperature Range: -55°C to +175°C
- Storage Temperature Range: -55°C to +175°C
- Thermal Resistance: 0.47°C/W Junction to Case

MCC Part Number	Device Marking
SICPT20120Y	SICPT20120Y

Peak Repetitive Reverse Voltage	V _{RRM}	1200V	
Surge Peak Reverse Voltage	V_{RSM}	1200V	
DC Reverse Voltage	V_{DC}	1200V	
Average Forward Current	I _F	20A	T _J =157°C
Peak Forward Surge Current	I _{FSM}	160A	T _C =25°C, t _p =10ms, Half Sine Pulse
Power Dissipation	P_D	319W	T _c =25°C

Note:1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds. 2. High Temperature Solder Exemptions Applied, see EU Directive Annex 7a.

Internal Structure:

PIN 1 OF CASE

20Amp Silicon Carbide Schottky Barrier Rectifier 1200 Volts



DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	NOTE
А	0.610	0.663	15.50	16.85	
В	0.815	0.839	20.70	21.30	
С	0.189	0.205	4.80	5.20	
D	0.2	242	6.	15	BSC.
Е	0.091	0.106	2.30	2.70	
F	0.772	0.796	19.62	20.22	
G		0.169		4.30	
Н	0.4	128	10	.88	BSC.
I	0.075	0.087	1.91	2.21	
J	0.044	0.054	1.11	1.36	
Κ	0.189	0.205	4.80	5.20	
0	0.073	0.085	1.85	2.15	
Р	0.087	0.103	2.21	2.61	
Q	0.020	0.030	0.51	0.75	
R	0.512	0.535	13.00	13.60	
S	0.640	0.663	16.25	16.85	
Т	0.134	0.150	3.40	3.80	Φ
U		0.287		7.30	Φ



Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Conditions	Тур.	Max.	Units
		I _F =20A, T _J =25°C	1.34	1.55	V
Forward Voltage	V _F	I _F =20A, T _J =175°C	1.86	2.70	V
Poverse Lookage Current	I _R	V _R =1200V, T _J =25°C	0.5	25	μA
Reverse Leakage Current		V _R =1200V, T _J =175°C	5		μA
Total Capacitive Charge	Q _C	V _R =800V	114		nC
		V _R =0V, f=1MHz	1552		pF
Total capacitance		V _R =400V, f=1MHz	107		pF
		V _R =800V, f=1MHz	79		pF
Capacitance Stored Energy	Ec	V _R =800V	29.3		μJ



Curve Characteristics





Curve Characteristics









Ordering Information

Device	Packing
SICPT20120Y-BP	Bulk: 30pcs/Tube

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. *Micro Commercial Components Corp*. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp*. and all the companies whose products are represented on our website, harmless against all damages. *Micro Commercial Components Corp*. products are sold subject to the general terms and conditions of commercial sale, as published at

https://www.mccsemi.com/Home/TermsAndConditions.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources**. MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.