

APPLICABLE STANDARD		SPECIFICATIONS							
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C (NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C (NOTE3)					
	OPERATING HUMIDITY RANGE	20 % TO 80 % (NOTES 2)	STORAGE HUMIDITY RANGE	40 % TO 70 % (NOTE3)					
	VOLTAGE	150 V AC/DC	CURRENT	1 A/pin					
	APPLICABLE CONNECTOR	DF13-*S-1.25C	APPLICABLE CONTACT	DF13(G)-2630SCF DF13-3032SCF					
CONSTRUCTION									
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.		X X				
MARKING	CONFIRMED VISUALLY.				X X				
ELECTRIC CHARACTERISTICS									
CONTACT RESISTANCE	100 m A (DC OR 1000 Hz).		30 mΩ MAX.		X -				
INSULATION RESISTANCE	100 V DC.		500 MΩ MIN.		X -				
VOLTAGE PROOF	500 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.		X -				
MECHANICAL CHARACTERISTICS									
MECHANICAL OPERATION	30 TIMES INSERTIONS AND EXTRACTIONS.		1) CONTACT RESISTANCE: 30 mΩ MAX. 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS.		X -				
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.		1) NO ELECTRICAL DISCONTINUITY OF 1μs. 2) NO DAMAGE, CRACK OR LOOSENESS OF PARTS.		X -				
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				X -				
ENVIRONMENTAL CHARACTERISTICS									
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→ 15 TO 35→+85→ 15 TO 35 °C TIME 30→ 2 TO 3→30→ 2 TO 3 min. UNDER 5 CYCLES.		1) CONTACT RESISTANCE: 30mΩ MAX. 2) INSULATION RESISTANCE: 500 MΩ MIN. 3) NO DAMAGE, CRACK OR LOOSENESS OF PARTS.		X -				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40 ± 2 °C, 90 TO 95 %, 96 h.				X -				
RESISTANCE TO SOLDERING HEAT	1) SOLDER BATH METHOD 250°C, FOR 10 sec. 2) MANUAL SOLDERING SOLDERING IRON TEMPERATURE :300°C, SOLDERING TIME : 3sec. NO STRENGTH ON CONTACT.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.		X -				
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 240°C FOR INSERTION DURATION, 3sec.		SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSED.		X -				
REMARKS									
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT. NOTE2: NO CONDENSING. NOTE3: APPLY TO PACKED CONDITION.									
COUNT		DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE				
									
Unless otherwise specified, refer to IEC 60512.			APPROVED	SJ. OKAMURA	20211217				
			CHECKED	SZ. ONO	20211217				
			DESIGNED	HT. SATO	20211217				
			DRAWN	SK. CHIBA	20211217				
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC-083673-05-00					
	SPECIFICATION SHEET		PART NO.	DF13-*P-1. 25DSA (05)					
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL536	 1/1				