



REV.	ECN NO.	REVISED	DATE

NOTE:




1.MATERIAL:

- a.HOUSING:PA66 BLACK
- b.CONTACT:304 STAINLESS STEEL
(SURFACE PLATING: Ni-PLATING)


SEE ORDERING INFORMATION

2.ELECTRIC:

- a.CONTACT RESISTANCE: 100 MILLIOHMS MAX
- b.INSULATION RESISTANCE: 100 MEGA OHMS MIN
- c.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
- d.OPERATING TEMPERATURE: -25° C~ +85° C



PCB Layout Diagram
Bottom View



ORDERING INFORMATION

BH-21700-B1BJ001

电池盒

电池型号

SMT 180° TYPE

PLATING:
A-Au1U"
J-Ni-PLATING
K-Sn-PLATING

MATERIAL:
1A-PBT BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK
5B-NYLON RESIN BLACK

工程部
2023-11-10
H. WANG

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND WangHeng	DATE 2023-11-10
WEIGHT:		CHKD ZhouRuicai	DATE 2023-11-10
SHEET 1 OF 1		APVD XueShunyong	DATE 2023-11-10
TITLE:		SCALE:	SIZE: A4
VIEW:		UNIT: mm	REV.: A/0
PART NO.:		OBJECT: MY	DRAW NO.:WD-CP-0357
BH-21700-B1BJ001		TITLE: 电池盒BH-21700-1J Ni SMT	

NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
3	TERMINAL(+)	1	304 Stainless Steel, T=0.35MM	Ni-Plating
2	TERMINAL(-)	1	304 Stainless Steel, T=0.35MM	Ni-Plating
1	HOUSING	1	PA66	BLACK