


| ID  | R <sub>DS(ON)</sub> (Typ) | VDSS |
|-----|---------------------------|------|
| 60A | 7.5mΩ                     | 100V |

**Applications:**

- Load Switch
- PWM Applications
- Power Managment

**Features:**

- Fast switching speed
- 100% avalanche tested
- Improved dv/dt capability


**Ordering Information**

| Part Number | Package | Marking   | Packing   | Qty.     |
|-------------|---------|-----------|-----------|----------|
| RS100N60G   | DFN5*6  | RS100N60G | Tape&reel | 5000 PCS |

**Absolute Maximun Ratings** Tc= 25℃ unless otherwise specified

| Symbol      | Parameter                                                                 | RS100N60G  | Units |
|-------------|---------------------------------------------------------------------------|------------|-------|
| VDSS        | Drain-to-Source Voltage                                                   | 100        | V     |
| ID          | Continuous Drain Current TC=25℃                                           | 60         | A     |
| ID          | Continuous Drain Current TC=100℃                                          | 38         |       |
| IDM         | Pulsed Drain Current (Note*1)                                             | 240        |       |
| PD          | Power Dissipation                                                         | 63         | W     |
| VGS         | Gate- to- Source Voltage                                                  | ±20        | V     |
| EAS         | Single Pulse Avalanche Engergy<br>L = 0.5mH, VDD = 50V, RG = 25 Ω, TC=25℃ | 90         | mJ    |
| TL TPKG     | Maximum Temperature for Soldering                                         | 300<br>260 | ℃     |
|             | Leads at 0.063in(1.6mm)from Case for 10 seconds                           |            |       |
|             | Package Body for 10 seconds                                               |            |       |
| TJ and TSTG | Operating Junction and Storage Temperature Range                          | -55 to 150 |       |

\* Drain Current Limited by Maximum Junction Temperature

Caution: Stresses greater than those listed in the“ Absolute Maximum Ratings” Table may cause permanent damage to the device.

### Thermal Resistance

| Symbol        | Parameter        | RS100N60G | Units  | Test Conditions                                                                                       |
|---------------|------------------|-----------|--------|-------------------------------------------------------------------------------------------------------|
| R $\theta$ JC | Junction-to-Case | 2.0       | °C / W | Drain lead soldered to water cooled heatsink, PD adjusted for a peak junction temperature of + 150 °C |

### OFF Characteristics TJ= 25°C unless otherwise specified

| Symbol | Parameter                           | Min. | Typ. | Max. | Units   | Test Conditions        |
|--------|-------------------------------------|------|------|------|---------|------------------------|
| BVDSS  | Drain- to- source Breakdown Voltage | 100  | --   | --   | V       | VGS=0V, ID=250 $\mu$ A |
| IDSS   | Drain- to- Source Leakage Current   | --   | --   | 1    | $\mu$ A | VDS=80V, VGS=0V        |
| IGSS   | Gate- to- Source Forward Leakage    | --   | --   | 100  | nA      | VGS=20V ,VDS=0V        |
|        | Gate- to- Source Reverse Leakage    | --   | --   | -100 |         | VGS=-20V ,VDS=0V       |

### ON Characteristics TJ=25°C unless otherwise specified

| Symbol  | Parameter                                      | Min. | Typ. | Max. | Units      | Test Conditions         |
|---------|------------------------------------------------|------|------|------|------------|-------------------------|
| RDS(on) | Static Drain- to- Source On-Resistance(Note*2) | --   | 7.5  | 8.5  | m $\Omega$ | VGS=10V, ID=20A         |
|         |                                                | --   | 10.5 | 12.5 | m $\Omega$ | VGS=4.5V, ID=10A        |
| VGS(TH) | Gate Threshold Voltage                         | 1.2  | --   | 2.5  | V          | VGS=VDS, ID=250 $\mu$ A |

### Resistive Switching Characteristics Essentially independent of operating temperature

| Symbol  | Parameter            | Min. | Typ. | Max. | Units | Test Conditions                               |
|---------|----------------------|------|------|------|-------|-----------------------------------------------|
| td(ON)  | Turn- on Delay Time  | --   | 17   | --   | nS    | VDS=50V<br>ID=20A<br>RG=3 $\Omega$<br>VGS=10V |
| trise   | Rise Time            | --   | 4    | --   |       |                                               |
| td(OFF) | Turn- OFF Delay Time | --   | 32   | --   |       |                                               |
| tfall   | Fall Time            | --   | 8    | --   |       |                                               |

### Dynamic Characteristics

Essentially independent of operating temperature

| Symbol | Parameter                       | Min. | Typ. | Max. | Units | Test Conditions               |
|--------|---------------------------------|------|------|------|-------|-------------------------------|
| Ciss   | Input Capacitance               | --   | 2122 | --   | pF    | VGS=0V<br>VDS=50V<br>f=100KHz |
| Coss   | Output Capacitance              | --   | 618  | --   |       |                               |
| Crss   | Reverse Transfer Capacitance    | --   | 25   | --   |       |                               |
| Qg     | Total Gate Charge               | --   | 41.8 | --   | nC    | VDS=50V<br>ID=20A<br>VGS=10V  |
| Qgs    | Gate- to- Source Charge         | --   | 9    | --   |       |                               |
| Qgd    | Gate-to-Drain(" Miller") Charge | --   | 10   | --   |       |                               |

### Source- Drain Diode Characteristics

| Symbol | Parameter                 | Min. | Typ. | Max. | Units | Test Conditions                   |
|--------|---------------------------|------|------|------|-------|-----------------------------------|
| IS     | Continuous Source Current | --   | --   | 60   | A     | Integral pn- diode<br>in MOSFET   |
| ISM    | Maximum Pulsed Current    | --   | --   | 240  | A     |                                   |
| VSD    | Diode Forward Voltage     | --   | --   | 1.2  | V     | IS=20A,VGS=0V                     |
| trr    | Reverse Recovery Time     | --   | 50   | --   | nS    | VGS=0V<br>IS=20A<br>di/dt=100A/μs |
| Qrr    | Reverse Recovery Charge   | --   | 71   | --   | nC    |                                   |

#### Notes:

- \* 1. Repetitive rating, pulse width limited by maximum junction temperature.
- \* 2. Pulse Test: Pulse width  $\leq 300\mu\text{s}$ , Duty Cycle  $\leq 1\%$

### Typical Feature Curve

Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Drain-to-Source On Resistance vs Drain Current




Figure 4. Body Diode Forward Voltage vs Source Current and Temperature




Figure 5. Capacitance Characteristics




Figure 6. Gate Charge Characteristics




Figure 7. Normalized Breakdown Voltage vs Junction Temperature




Figure 8. Normalized On Resistance vs Junction Temperature




Figure 9. Maximum Continuous Drain Current vs Case Temperature




Figure 10. Maximum Power Dissipation vs Case Temperature




Figure 11. Drain-to-Source On Resistance vs Gate Voltage and Drain Current




Figure 12. Maximum Safe Operating Area





Figure 13. Maximum Effective Transient Thermal Impedance, Junction-to-Case





## Test ircuits and Waveforms




Figure A.  
Gate Charge Test Circuit




Figure B.  
Gate Charge Waveform




Figure C.  
Resistive Switching Test Circuit




Figure D.  
Resistive Switching Waveforms

## Test Circuits and Waveforms




Figure E. Diode Reverse Recovery Test Circuit




Figure F. Diode Reverse Recovery Waveform






Figure G. Unclamped Inductive Switching Test Circuit



$$E_{AS} = \frac{I_{AS}^2 L}{2}$$

Figure H. Unclamped Inductive Switching Waveforms

**Package outline drawing(DFN5\*6 Unit: mm )**



| Dimensions In<br>Millimeterer |      |      |      |
|-------------------------------|------|------|------|
| Symbol                        | MIN  | TYP  | MAX  |
| A                             | 5.90 | 6.00 | 6.10 |
| a                             | 3.91 | 4.01 | 4.11 |
| A2                            | 5.70 | 5.75 | 5.80 |
| B                             | 4.90 | 5.00 | 5.10 |
| b                             | 3.37 | 3.47 | 3.57 |
| B1                            | 4.80 | 4.90 | 5.00 |
| C                             | 0.90 | 0.95 | 1.00 |
| L                             | 0.35 | 0.40 | 0.45 |
| l                             | 0.06 | 0.13 | 0.20 |
| L1                            | 1.10 | —    | —    |
| l1                            | —    | —    | 0.10 |
| L2                            | 1.17 | 1.27 | 1.37 |
| L4                            | 0.21 | 0.26 | 0.34 |
| L6                            | 0.51 | 0.61 | 0.71 |
| L7                            | 0.51 | 0.61 | 0.71 |
| P                             | 1.00 | 1.10 | 1.20 |
| θ                             | 8°   | 10°  | 12°  |
| Φ                             | 1.10 | 1.20 | 1.30 |



**Disclaimers:**

Reasunos Semiconductor Technology Co.Ltd (Reasunos) reserves the right to make changes without notice in order to improve reliability,function or design and to discontinue any product or service without notice .Customers should obtain the latest relevant information before orders and should verify that such information in current and complete.All products are sold subject to Reasunos's terms and conditions supplied at the time of orderacknowledgement.

Reasunos Semiconductor Technology Co.Ltd warrants performance of its hardware products to the specifications at the time of sale.Testing,reliability and quality control are used to the extene Reasunos deems necessary to support this warrantee. Except where agreed upon by contr- actual agreement,testing of all parameters of each product is not necessarily performed.

Reasunos Semiconductor Technology Co.Ltd does not assume any liability arising from the use of any product or circuit designs described herein.Customers are responsible for their products and applications using Reasunos's components.To minimize risk,customers must provide adequate design and operating safeguards.

Reasunos Semiconductor Technology Co.Ltd does not warrant or convey any license either expressed or implied under its patent rights,nor the rights of others.Reproduction of information in Reasunos's data sheets or data books is permissible only if reproduction is without modification or alteration.Reproduction of this information with any alteration is an unfair and deceptive business practice. Reasunos Semiconductor Technology Co.Ltd is not responsible or liable for such altered documentation.

Resale of Reasunos's products with statements different from or beyond the parameters stated by Reasunos Semiconductor Technology Co.Ltd for that product or service voids all express or implied warranties for the associated Reasunos's product or service and is unfair and deceptive business practice. Reasunos Semiconductor Technology Co.Ltd is not responsible or liable for such statements.

**Life Support Policy:**

Reasunos Semiconductor Technology Co.Ltd's Products are not authorized for use as critical components in life support devices or systems without the expressed written approval of Reasunos Semiconductor Technology Co.Ltd.

As used herein:

1. Life support devices or systems are devices or systems which: a.are intended for surgical implant into the human body, b.support or sustain life, c.whose failure to when properly used in accordance with instructions for used provided in the laeling,can be reasonably expected to result in significant injury to the user.

2.A critical component is any component of a life support device or system whose failure to system whose failure to perform can be reasonably expected to cause the failure of the life support device or system,or to affect its safety or effectiveness.