



ESD5Z Series

Transient Voltage Suppressors

DESCRIPTION

The ESD5Z Series is designed to protect voltage sensitive components from ESD and transient voltage events. Excellent clamping capability, low leakage, and fast response time, make these parts ideal for ESD protection on designs where board space is at a premium. Because of its small size, it is suited for use in cellular phones, portable devices, digital cameras, power supplies and many other portable applications.

FEATURES

- ✧ IEC61000-4-2 Level 4 ESD Protection
- ✧ Protects one directional I/O line
- ✧ Low clamping voltage
- ✧ Working voltages : 2.5V, 3.3V, 5V, 6V, 7V, 12V, 15V
- ✧ Low leakage current

MECHANICAL DATA

- ✧ SOD-523 package
- ✧ Flammability Rating: UL 94V-0
- ✧ Packaging: Tape and Reel
- ✧ High temperature soldering guaranteed: 260°C/10s
- ✧ Reel size: 7 inch


ORDERING INFORMATION

- ✧ Device: ESD5ZXXX
- ✧ Package: SOD-523
- ✧ Material: Halogen free
- ✧ Packing: Tape & Reel
- ✧ Quantity per reel: 3,000pcs

APPLICATIONS

- ✧ Cell Phone Handsets and Accessories
- ✧ Microprocessor based equipment
- ✧ Personal Digital Assistants (PDA's)
- ✧ Notebooks, Desktops, and Servers
- ✧ Portable Instrumentation
- ✧ Peripherals
- ✧ Pagers

PIN CONFIGURATION



PACKAGE OUTLINE





ESD5Z Series

Transient Voltage Suppressors

ABSOLUTE MAXIMUM RATING

Symbol	Parameter	Value	Units
V_{ESD}	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	± 30 ± 22	kV
ESD	ESD Voltage per human body model ESD Voltage per machine model	16 400	kV V
P_D	Total Power Dissipation on FR-5 Board (Note 1) @ $T_a=25^{\circ}\text{C}$	150	mW
T_J, T_{STG}	Junction and Storage Temperature	-55/+150	$^{\circ}\text{C}$
T_L	Lead Solder Temperature – Maximum (10 Second Duration)	260	$^{\circ}\text{C}$

These ratings are limiting values above which the serviceability of the diode may be impaired

Note 1. FR-5=1.0x0.75x0.62 in.

ELECTRICAL CHARACTERISTICS ($T_{amb}=25^{\circ}\text{C}$)

PART NUMBER	DEVICE MARKING	V_{RWM}	I_R	V_B	I_T	V_C		V_C		P_{PK}	C_J
		(V)	(μA)	(V)	(mA)	(V)		(V)		(W)	(pF)
		Max	Max	Min		Max	@A	Max	@A	Max	Max
ESD5Z2V5	ZD + code	2.5	6.0	4.0	1	9.0	5.0	11.5	9.0	104	145
ESD5Z3V3	ZE + code	3.3	0.90	5.0	1	10.0	5.0	14.0	7.5	105	105
ESD5Z5V0	ZF + code	5.0	0.08	6.2	1	11.6	5.0	15.0	7.0	105	80
ESD5Z6V0	ZG + code	6.0	0.05	6.8	1	13.5	5.0	17.5	6.0	105	70
ESD5Z7V0	ZH + code	7.0	0.03	7.5	1	14.0	5.0	18.0	6.0	108	65
ESD5Z12V	ZM + code	12.0	0.03	14.1	1	20.0	1.0	26.0	4.0	104	45
ESD5Z15V	ZN + code	15.0	0.50	16.0	1	23.0	1.0	30.0	4.0	120	28



ESD5Z Series

Transient Voltage Suppressors

ELECTRICAL CHARACTERISTICS CURVE

Fig 1 8/20 μ s Waveform per IEC61000-4-5




Fig 2 Contact Discharge Current Waveform per IEC 61000-4-2)




Fig 3 Voltage vs Capacitance




Fig 4 Voltage vs Capacitance




Fig 5 Clamping Voltage vs Peak Pulse Current





Fig 6 Clamping Voltage vs Peak Pulse Current






ESD5Z Series

Transient Voltage Suppressors

SOD-523 PACKAGE OUTLINE DIMENSIONS



Note: Dimensions are exclusive of Burrs, Mold Flash & Tie Bar extrusions.