






REV.	ECN NO.	REVISED	DATE

NOTE:

- 1.MATERIAL:  
 a.HOUSING:NYLON BLACK UL94V-0  
 b.CONTACT:STEEL  
 (SURFACE PLATING: Au 1U")  
 SEE ORDERING INFORMATION
- 2.ELECTRIC:  
 a.DIELECTRIC VOLTAGE: 500V AC ONE SEC LEVEL  
 b.OPERATING TEMPERATURE: -10° C~ +80° C




ORDERING INFORMATION

BH-AA-B\*\*\*034

电池盒  
 电池型号  
 SMT 180° TYPE

PLATING:  
 A-Au1U"  
 J-Ni100U"~120U"  
 K-Sn100U"~120U"

MATERIAL:  
 1A-PBT BLACK  
 1B-PA66 BLACK  
 2A-PPA BROWN  
 2B-PPA BLACK  
 3A-PPS BROWN  
 3B-PPS BLACK  
 4A-LCP WHITE  
 4B-LCP BLACK  
 5A-PA9T BLACK  
 5B-NYLON BLACK



PCB Layout Diagram  
TOP View

UNLESS OTHERWISE SPECIFIED TOLERANCES		<b>MYOUNG 美用</b> <a href="http://www.meiyangdz.com">www.meiyangdz.com</a>	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND YangFeng	DATE 2020-05-13
WEIGHT: SHEET 1 OF 1		CHKD ZhouRuicai	DATE 2020-05-13
		APVD XueShunyong	DATE 2020-05-13
TITLE: 电池盒BH-AA-2J Au SMT 负极弹簧		PART NO.:	
SCALE: VIEW:		BH-AA-B5BA034	
UNIT: mm REV.: A/0		OBJECT: MY DRAW NO.:WD-CP-0218	

2	TERMINAL	4	STEEL, T=0.3mm	Au-Plating
1	HOUSING	1	NYLON 94V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR