






POSITION 1
POSITION 2



SUGGESTED PANEL CUTOUT



SCHEMATIC



SPECIFICATIONS

FUNCTION:
2P1T OFF-ON with Actuator Lock

RATINGS:
ANSI/UL 1054 and CAN/CSA C22.2 No. 55 (E194579):
20A 125VAC [cURus]
12A 250VAC [cURus]

ELECTRICAL LIFE:
6,000 Cycles [cURus]

TEMPERATURE:
Operating: -20°C to 65°C [cURus]

APPROVALS:

MATERIALS

UPPER BODY:
Polyamide 6/6 (PA66)

LOWER BODY:
Phenolic

ACTUATOR:
Polyamide 6/6 (PA66)

ACTUATOR LOCK:
Polyamide 6/6 (PA66)

CONTACTS:
Silver Plated Copper

TERMINALS:
Brass

COLORS AND MARKINGS

UPPER BODY:
Black

LOWER BODY:
Black

ACTUATOR:
Red

ACTUATOR LOCK:
Yellow

MARKINGS:
ON/OFF

MARKING COLOR:
White

OBJECT ID: 000000974



E-SWITCH®



HY7-42D-196

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

B	UPDATE TERMINAL NUMBERS TO MATCH PART	101068	06/22/22	JS
A	INITIAL RELEASE	PCR00195	09/11/05	CAB
REV.	DESCRIPTION	PCR	DATE	DRAWN BY

DIMENSIONS	
INCHES [MILLIMETERS]	
GENERAL TOLERANCES ±0.016 [±0.4] / ±1°	
SCALE	PROJECTION
DRAWING NOT TO SCALE	

DRAWING NUMBER	DATE	REVISION
34-HY742D196	NOVEMBER 05, 2009	B