

## SEK-18 SV MA LP ANG29 60P PL3




Image is for illustration purposes only. Please refer to product description.

Part number	09 18 560 7323
Specification	SEK-18 SV MA LP ANG29 60P PL3
HARTING eCatalogue	<a href="https://b2b.harting.com/09185607323">https://b2b.harting.com/09185607323</a>

### Identification

Category	Connectors
Series	SEK Low-profile
Element	Male connector
Description of the contact	Angled

### Version

Termination method	Wave soldering termination
Connection type	PCB to cable Motherboard to daughtercard
Number of contacts	60
Termination length	2.9 mm

### Technical characteristics

Contact rows	2
Contact spacing (termination side)	2.54 mm
Rated current	1 A
Insulation resistance	$>10^9 \Omega$
Contact resistance	$\leq 20 \text{ m}\Omega$
Limiting temperature	-55 ... +125 °C
Insertion and withdrawal force	$\leq 180 \text{ N}$
Performance level	3 acc. to IEC 60603-13
Mating cycles	$\geq 50$

## Technical characteristics

Test voltage U <sub>r.m.s.</sub>	1 kV
Isolation group	IIIa (175 ≤ CTI < 400)

## Material properties

Material (insert)	Thermoplastic resin (PBT)
Colour (insert)	Grey
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Antimony trioxide Lead Nickel
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 60603-13
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Railway classification	F3/I3

## Commercial data

Packaging size	50
Net weight	8.12 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140035188
ETIM	EC002637

## Commercial data

eCl@ss

27460201 PCB connector (board connector)

### Cross section of solder termination

