


Features

- Heatsink structure
- Low profile, typical thickness 0.8mm
- Low leakage current
- Super Low VF Schottky barrier diodes
- Moisture sensitivity: level 1, per J-STD-020
- High temperature soldering guaranteed: 260°C/10 seconds



Package: iSGA
(SOD-123HS)

Absolute Maximum Ratings $T_A=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	GSPSL26	Unit
Maximum repetitive peak reverse voltage	V_{RRM}	60	V
Maximum RMS voltage	V_{RMS}	42	V
Maximum DC blocking voltage	V_{DC}	60	V
Maximum average forward rectified current	$I_{F(AV)}$	2.0	A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I_{FSM}	50	A
Operating junction temperature range	T_J	- 55 to + 125	$^{\circ}\text{C}$
Storage temperature range	T_{STG}	- 55 to + 150	$^{\circ}\text{C}$

Electrical Characteristics $(T_A=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Test Conditions	Symbol	GSPSL26	Unit
Maximum instantaneous forward voltage	$I_F=1\text{A}, T_A=25^{\circ}\text{C}$	V_F	0.45	V
	$I_F=2\text{A}, T_A=25^{\circ}\text{C}$		0.50	
Maximum DC reverse current at rated DC blocking voltage	$T_A=25^{\circ}\text{C}$	I_R	200	μA
	$T_A=125^{\circ}\text{C}$		100	mA
Typical junction capacitance	4.0 V, 1 MHz	C_J	125	pF
Typical thermal resistance ¹⁾	junction to ambient	$R_{\theta JA}$	85	$^{\circ}\text{C}/\text{W}$
	junction to mount	$R_{\theta JM}$	30	

Note:1), The thermal resistance from junction to ambient, case or mount, mounted on P.C.B with 5×5mm copper pads, 2 OZ, FR4 PCB

Typical Electrical Characteristic Curves

($T_A=25^\circ\text{C}$ unless otherwise noted)




Figure 1. Forward Current Derating Curve




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current




Figure 3. Typical Instantaneous Forward Characteristics




Figure 4. Typical Reverse Characteristics






Figure 5. Typical Junction Capacitance

Package Outline Dimensions



Package	iSGA	
Unit:mm	MIN	MAX
A	0.75	0.90
B	0.85	1.05
B1	0.85	1.05
C	0.1	0.25
D	1.9	2.1
E	2.9	3.1
L1	2.0	2.45
L2	0.4	0.85
L3	1.3	1.7
HE	3.5	3.9

Soldering footprint



Packing Information

Packing Quantities

Reel size	Quantity/reel	Quantity/inner Box	Quantity/Carton
7"	3K	30K	120K

Tape & Reel Specification

