



Click [here](#) for the 3D model.

Dimensions

| | |
|----|--------------------|
| L | 41.5mm +0.3/-0.7mm |
| H | 15mm +0.1/-0.7mm |
| T | 24mm +0.3/-0.7mm |
| S | 37.5mm +/-0.4mm |
| LL | 25mm +2/-1mm |
| F | 1mm +/-0.4mm |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | Tray |
| Packaging Quantity | 108 |

General Information

| | |
|--------------------------|---|
| Series | R75 |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | Pulse |
| RoHS | Yes |
| Lead | Wire Leads |
| AEC-Q200 | No |
| Typical Component Weight | 15.4 g |
| Miscellaneous | Above 85C DC voltage derating is 2%/C and AC voltage derating is 1.25%/C. |

Specifications

| | |
|-----------------------|--|
| Capacitance | 2.7 uF |
| Capacitance Tolerance | 5% |
| Voltage AC | 220 VAC |
| Voltage DC | 400 VDC |
| Temperature Range | -55/+105°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 0.06% 1kHz, 0.08% 10kHz |
| Insulation Resistance | 11.111 GOhms |
| Max dV/dt | 70 V/us |
| Resistance | 8.842 mOhms (100kHz) |
| Ripple Current | 9.632 Amps (100kHz 85C), 189 Amps (Peak) |
| Inductance | 20 nH |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.