

# SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/pc/products/1108101>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection with M12 standard thread, push-pull, with O-ring, for 2-piece K-, L-, and M-coded THR contact carriers

## Your advantages

- Manufacturer-independent M12 push-pull locking system for maximum availability
- Easy and quick cabling of devices and systems in hard-to-reach areas
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Flexible PCB assembly: two-piece connectors for wave and THR soldering

## Commercial data

Item number	1108101
Packing unit	20 pc
Minimum order quantity	20 pc
Product key	ABQABC
GTIN	4063151011499
Weight per piece (including packing)	10.99 g
Weight per piece (excluding packing)	10 g
Customs tariff number	85366990
Country of origin	DE

# SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/pc/products/1108101>

## Technical data

### Notes

General	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
General	Lock nut is included in the scope of delivery

### Product properties

Product type	Panel mounting base
--------------	---------------------

### Connection data

Connection method	THR- und Wellenlötkontakte
-------------------	----------------------------

### Material specifications

Material	Brass, nickel-plated
Flammability rating according to UL 94	V0
Seal material	FKM
Material of grip body	Brass, nickel-plated
Material for screw connection	Brass, nickel-plated

### Connector

#### Connection 1

Head design	Pin
Head thread type	M12
Head locking type	Push-Pull

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked) IP67, when in locked state
Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket) -40 °C ... 85 °C (without mechanical actuation)

### Standards and regulations

M12

# SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/pc/products/1108101>

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-010
Note	Push-pull

## Mounting

Mounting type	Rear mounting M15 x 1
Connection method	THR- und Wellenlötkontakte

# SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/pc/products/1108101>

## Classifications

### ECLASS

ECLASS-11.0	27440224
ECLASS-12.0	27440224
ECLASS-13.0	27440224

### ETIM

ETIM 9.0	EC003556
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# SACC-BP-M-M12-THR PW PP - Housing screw connection



1108101

<https://www.phoenixcontact.com/pc/products/1108101>

## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

# SACC-BP-M-M12-THR PW PP - Housing screw connection

1108101

<https://www.phoenixcontact.com/pc/products/1108101>

## Accessories

### PROT-M12 FS - Sealing cap

1560251

<https://www.phoenixcontact.com/pc/products/1560251>



M12 sealing cap for unoccupied M12 plugs of the sensor/actuator cable, flush-type plugs and I/O devices in the field

---

### PROT-M12 FS-M - Sealing cap

1430488

<https://www.phoenixcontact.com/pc/products/1430488>



M12 metal sealing cap for unoccupied M12 plugs of the sensor/actuator cable, flush-type plugs and I/O devices in the field

---

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstraße 8  
D-32825 Blomberg  
+49 (0) 5235-3 00  
[info@phoenixcontact.com](mailto:info@phoenixcontact.com)