


# Data sheet

## 10352.1 PK 300/8/10,16 GN



PCB terminal, Screw connection, No. of poles: 8, Width: 76.8 mm, Colour: Green

### Business data

|                                            |                   |
|--------------------------------------------|-------------------|
| Article number                             | <u>10352.1</u>    |
| Article name                               | PK 300/8/10,16 GN |
| GTIN (EAN)                                 | 4044211007744     |
| Packaging unit                             | 50                |
| Quantity unit                              | PC                |
| Packaging type                             | Carton            |
| Type of banding                            | Without           |
| Weight per piece (not including packaging) | 12.9 g            |
| Weight per piece (including packaging)     | 13.5 g            |
| Unit of weight                             | G                 |
| Customs number                             | 85369010          |
| Country of origin                          | QU                |
| Prio-Article                               | 10352.1           |

### Technical data

#### Dimensions

|                            |          |
|----------------------------|----------|
| Length                     | 12.5 mm  |
| Length of the pin          | 4.5 mm   |
| Width                      | 76.8 mm  |
| Width left                 | 2.54 mm  |
| Width right                | 3.14 mm  |
| Height                     | 12.5 mm  |
| Drill hole diameter        | 1.3 mm   |
| Diameter of connecting pin | 1 mm     |
| Pitch                      | 10.16 mm |

#### Ratings

|                       |                     |
|-----------------------|---------------------|
| Rated voltage         | 250 V               |
| Rated current         | 24 A                |
| Rated cross-section   | 1.5 mm <sup>2</sup> |
| Rated impulse voltage | 2 kV                |
| Overvoltage category  | III                 |
| Contamination degree  | 3                   |

### Technical data

#### Connection data

|                                                         |                            |
|---------------------------------------------------------|----------------------------|
| Connection principle                                    | Screw connection           |
| Connection type of PCB                                  | Solder connection          |
| Type of attachment to circuit board                     | Connecting contact         |
| Angle of PCB/wire connection                            | 45°/135° (slanted upwards) |
| No. of poles                                            | 8                          |
| Number of levels                                        | 1                          |
| Wire cross-section single-core (rigid) / stranded, min. | 0.14 mm <sup>2</sup>       |
| Wire cross-section single core (rigid)/stranded, max.   | 2.5 mm <sup>2</sup>        |
| Wire cross-section stranded, min.                       | 0.14 mm <sup>2</sup>       |
| Wire cross-section stranded, max.                       | 1.5 mm <sup>2</sup>        |
| Wire cross-section stranded with wire-end ferrules,min. | 0.25 mm <sup>2</sup>       |
| Wire cross-section stranded with wire-end ferrules,max. | 1.5 mm <sup>2</sup>        |
| Wire cross-section AWG, min.                            | 22                         |
| Wire cross-section AWG, max.                            | 12                         |
| Stripping length                                        | 7 mm                       |
| Screw threading                                         | M 2,6                      |
| Torque                                                  | 0.4 Nm                     |

#### Materials

|                           |               |
|---------------------------|---------------|
| Insulation housing        | Polyamide 6.6 |
| Flammability class UL 94  | V-0           |
| Working temperature, min. | -30 °C        |
| Working temperature, max. | 105 °C        |
| Clamping element          | Brass         |
| Screws                    | Steel         |
| Soldering lug             | Copper alloy  |

### Technical data

#### Further technical data

|                                                |                             |
|------------------------------------------------|-----------------------------|
| Storage temperature, min.                      | -40 °C                      |
| Storage temperature, max.                      | 105 °C                      |
| Insulation resistance                          | 1*10 <sup>13</sup> Ohm x cm |
| Creepage-current resistance                    | CTI 600                     |
| Glow wire flammability index GWFI              | GWFI 850                    |
| GWFI after-glow time                           | 30 Sek.                     |
| Glow wire ignition temperature GWIT            | GWIT 775 °C                 |
| GWIT exposure time                             | 5 Sek.                      |
| Connection cycles, in compliance with standard | 5                           |
| Recommended wave soldering temperature         | 265 °C                      |
| Recommended wave soldering duration, min.      | 3 Sek.                      |
| Recommended wave soldering duration, max.      | 4 Sek.                      |

#### Environmental Product Compliance

|                                |           |
|--------------------------------|-----------|
| REACH Conform                  | No        |
| REACH Candidate Substance Note | No        |
| REACH CAS 1 Percent minimal    | 0.1 %     |
| REACH CAS 1 Percent maximum    | 4 %       |
| REACH CAS 1 Number             | 7439-92-1 |
| RoHS Exception rule            | 6c        |

### Approvals

#### cUL Recognized

|                                           |              |
|-------------------------------------------|--------------|
| cUL approval                              | C22.2 No 158 |
| cUL Usegroup D: rated voltage             | 300 V        |
| cUL Usegroup D: rated current             | 15 A         |
| cUL wire cross-section stranded AWG, min. | 22           |
| cUL wire cross-section stranded AWG, max. | 12           |
| cUL torque                                | 0.5 Nm       |
| cUL wire material                         | Cu           |
| cUL Recognized                            | 1            |

#### UL Recognized

|                                          |            |
|------------------------------------------|------------|
| UL approval                              | UL 1059    |
| UL Usegroup B: rated voltage             | 600 V      |
| UL Usegroup B: rated current             | 16 A       |
| UL Usegroup C: rated voltage             | 600 V      |
| UL Usegroup C: rated current             | 16 A       |
| UL Usegroup D: rated voltage             | 300 V      |
| UL Usegroup D: rated current             | 15 A       |
| UL wire cross-section stranded AWG, min. | 22         |
| UL wire cross-section stranded AWG, max. | 12         |
| UL torque                                | 4.43 Lb In |
| UL wire material                         | Cu         |
| UL factory wiring                        | 1          |
| UL field wiring                          | 1          |
| UL Recognized                            | 1          |

### Approvals

#### VDE approval

|                                                     |                     |
|-----------------------------------------------------|---------------------|
| VDE approval                                        | DIN EN 60998        |
| VDE approval granted                                | yes                 |
| VDE rated voltage                                   | 250 V               |
| VDE rated current                                   | 24 A                |
| VDE rated current wire cross-section rigid, max.    | 24 A                |
| VDE rated current wire cross-section stranded, max. | 24 A                |
| VDE rated impulse voltage                           | 2 kV                |
| VDE wire cross-section rigid, min.                  | 0.5 mm <sup>2</sup> |
| VDE wire cross-section rigid, max.                  | 2.5 mm <sup>2</sup> |
| VDE wire cross-section stranded, min.               | 0.5 mm <sup>2</sup> |
| VDE wire cross-section stranded, max.               | 1.5 mm <sup>2</sup> |
| VDE screw threading                                 | M 2,6               |
| VDE torque                                          | 0.4 Nm              |
| VDE overvoltage category                            | III                 |
| VDE contamination degree                            | 3                   |






Data sheet

10352.1 PK 300/8/10,16 GN



Media

M2.6



---

**Accessories**

---