


171457-1

✓ ACTIVE

TE Internal #: 171457-1

PCB Mount Header, Vertical, Wire-to-Board, 21 Position, 5 mm [.197 in] Centerline, Fully Shrouded, Tin (Sn), Through Hole - Screw, Natural

[View on TE.com >](#)[Connectors > PCB Connectors > PCB Headers & Receptacles](#)Connector System: **Wire-to-Board**Number of Positions: **21**Number of Rows: **2**Centerline (Pitch): **5 mm [.197 in]**PCB Mount Orientation: **Vertical**

Features

Product Type Features

Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
PCB Connector Assembly Type	PCB Mount Header

Configuration Features

Number of Positions	21
Number of Rows	2
PCB Mount Orientation	Vertical

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Tab

Termination Features

Termination Method to Printed Circuit Board	Through Hole - Screw
---	----------------------

Mechanical Attachment

Connector Mounting Type	Board Mount
Mating Alignment	With
PCB Mount Alignment	With
PCB Mount Retention	Without

Housing Features

Centerline (Pitch)	5 mm [.197 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
-----------------------------	-----------------------------

Packaging Features

Packaging Type	Tray
----------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on


requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 171365-1
MIC CAP 21P H

Customers Also Bought




TE Part #1393310-2
VCFM-1000-FROM SEC



TE Part #171826-2
2POS POST HEADER ASSY



TE Part #170048-2
110 FASTON,REC.,24-20 AWG,TPBR



TE Part #796095-2
SLD CPC RCPT ASY,11-4,STD SEX



TE Part #353718-2
DYNAMIC D-3 TAB CONT. 3L AU 0.38
L/P



TE Part #1-316130-5
DYNAMIC D-3200 HDR ASSY 5P H



TE Part #1318123-1
DYNAMIC D2100 HDR V ASSY 3P



TE Part #171363-1
MULTI INTERLOCK CONN HSG



TE Part #2176082-9
EP 3W (S) 220R 5%

Documents

[CAD Files](#)

[3D PDF](#)

English

[Customer View Model](#)

[ENG_CVM_171457-1_K1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_171457-1_K1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_171457-1_K1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Multi-Interlock Mark II Connector for Printed Circuit Board](#)

Japanese

[Product Specification](#)

Japanese

[Multi-Interlock Mark II Connector for Wire to Board Termination](#)

English

[Product Specification](#)

English

Product Environmental Compliance

[TE Material Declaration](#)

English

Agency Approvals

[Agency Approval Document](#)

English