


电话：0769-82320511-867



P.C.B LAYOUT

Model No.	POS.1	POS.2	POS.1
	2AS4	MOM	OFF
Teram Comm	2-3	OPEN	2-1
SCHEMATIC			

SPECIFICATION

1. Rating : 3A max. @ 120 VAC.
1A max. @ 250 VAC.
2. Contact resistance: $\leq 20m\Omega$.
3. Insulation resistance: $\geq 1000M\Omega$ (DC1000V).
4. Withstanding voltage: 1000VAC .
5. Operating Force: $200\pm 100gf$
6. life test: 50,000 cycles.
7. Operation temperature range: $-25^{\circ}C \sim 85^{\circ}C$.
8. Sign"* "is importance dimension

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		NO	DATE	REVISIONS		BY	APPD
8					< 1.5: $\pm 0.1mm$ > 1.5~5.0: $\pm 0.25mm$ > 5.0: $\pm 0.3mm$							
7							ANGULAR $\pm 1^{\circ}$					
5	TERMINALS	BRASS	3	Au-PLATED								
4	CONTACT	BRASS	1	Au-PLATED	TITLE: TOGGLE SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
3	ACTUATOR	BRASS	1	Cr-PLATED	MODEL: 2AS4T1A1M2RES			SCALE: 1:1		CHK'D		
2	BUSHING	PA66	1		DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司					APPD		
1	CASE	PA66	1									PRO.AGL: