

**AEP 3C 4 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

End plates are fitted to the open side of the last modular terminal before the end bracket. The use of an end plate ensures the function of the modular terminal and the specified rated voltage. It guarantees protection against contact with live parts and makes the final terminal finger-proof.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | A-series, End plate        |
| Order No.  | <a href="#">2486640000</a> |
| Type       | AEP 3C 4 BK                |
| GTIN (EAN) | 4050118497458              |
| Qty.       | 20 pc(s).                  |

## AEP 3C 4 BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 32.35 mm | Depth (inches)  | 1.274 inch |
| Height     | 71.9 mm  | Height (inches) | 2.831 inch |
| Width      | 2.1 mm   | Width (inches)  | 0.083 inch |
| Net weight | 2.55 g   |                 |            |

## Temperatures

|                                  |                |                                  |        |
|----------------------------------|----------------|----------------------------------|--------|
| Storage temperature              | -25 °C...55 °C | Continuous operating temp., min. | -60 °C |
| Continuous operating temp., max. | 130 °C         |                                  |        |

## Material data

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Material                  | Wemid | Colour | black |
| UL 94 flammability rating | V-0   |        |       |

## System specifications

|         |           |
|---------|-----------|
| Version | End plate |
|---------|-----------|

## Additional technical data

|         |     |                   |     |
|---------|-----|-------------------|-----|
| Snap-on | Yes | With snap-in pegs | Yes |
|---------|-----|-------------------|-----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000886    | ETIM 7.0    | EC000886    |
| ETIM 8.0    | EC000886    | ETIM 9.0    | EC000886    |
| ECLASS 9.1  | 27-14-11-33 | ECLASS 10.0 | 27-14-11-33 |
| ECLASS 11.0 | 27-14-11-33 | ECLASS 12.0 | 27-14-11-33 |
| ECLASS 13.0 | 27250301    |             |             |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                                             |                                                              |
|---------------------------------------------|--------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Confirmation of Standards EN 45545-2_2020-10</a> |
| Engineering Data                            | <a href="#">CAD data – STEP</a>                              |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>              |
| Catalogues                                  | <a href="#">Catalogues in PDF-format</a>                     |