

T495D337M006ZTE045

Obsolete

B450, Tantalum, MnO2 Tantalum, 330 uF, 20%, 6.3 VDC, SMD, Molded, Low ESR, Surge Robust, 45 mOhms, 7343, Height Max = 3.1mm



Dimensions	
Footprint	7343
L	7.3mm +/-0.3mm
W	4.3mm +/-0.3mm
H	2.8mm +/-0.3mm
S	1.3mm +/-0.3mm
F	2.4mm +/-0.1mm
K	1.8mm TYP

Packaging Specifications	
Packaging	T&R, 178mm
Packaging Quantity	750

General Information	
Series	B450
Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, Molded, Low ESR, Surge Robust
Features	Low ESR, Surge Robust
RoHS	Yes
Termination	Tin
AEC-Q200	No
Notes	Obsolete. Old Part Number [Obsolete] Was B45006D3379M456.

Specifications	
Capacitance	330 uF
Capacitance Tolerance	20%
Voltage DC	6.3 VDC (85C), 4.22 VDC (125C)
Temperature Range	-55/+125°C
Rated Temperature	85°C
Dissipation Factor	12%
Failure Rate	N/A
Resistance	0.045 Ohms (100kHz)
Ripple Current	1830 mAmps (25C), 1647 mAmps (85C), 732 mAmps (125C)
Leakage Current	20.8 uA

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.