

# DS-PTV 2,5/4 - Cover segment

1083618

<https://www.phoenixcontact.com/us/products/1083618>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover segment, depth: 22 mm, width: 0.8 mm, height: 33.1 mm, color: gray

## Commercial data

Item number	1083618
Packing unit	1 pc
Minimum order quantity	50 pc
Sales key	BE29
Product key	BE2Z1X
GTIN	4055626819181
Weight per piece (including packing)	0.841 g
Weight per piece (excluding packing)	0.841 g
Customs tariff number	85389099
Country of origin	CN

# DS-PTV 2,5/4 - Cover segment

1083618

<https://www.phoenixcontact.com/us/products/1083618>



## Technical data

### Product properties

Product type	End cover
--------------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	V0

### Dimensions

Width	0.8 mm
Height	33.1 mm
Depth	22 mm

### Notes

General	A cover segment should be used if terminal blocks with a higher number of terminal points cannot be covered by the contour of another terminal block.
---------	---

# DS-PTV 2,5/4 - Cover segment

1083618

<https://www.phoenixcontact.com/us/products/1083618>



## Classifications

### ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

### ETIM

ETIM 9.0	EC000886
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# DS-PTV 2,5/4 - Cover segment



1083618

<https://www.phoenixcontact.com/us/products/1083618>

## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)