


T495W107M010ZTE1507280

Obsolete

B450, Tantalum, MnO2 Tantalum, 100 uF, 20%, 10 VDC, SMD, Molded, Low Profile, Low ESR, Surge Robust, 150 mOhms, 7343, Height Max = 1.5mm



| General Information |                                                           |
|---------------------|-----------------------------------------------------------|
| Series              | B450                                                      |
| Dielectric          | MnO2 Tantalum                                             |
| Style               | SMD Chip                                                  |
| Description         | SMD, Molded, Low Profile, Low ESR, Surge Robust           |
| Features            | Low Profile, Low ESR, Surge Robust                        |
| RoHS                | Yes                                                       |
| Termination         | Tin                                                       |
| AEC-Q200            | No                                                        |
| Notes               | Obsolete. Old Part Number [Obsolete] Was B45010X1076M157. |

| Specifications        |                                                    |
|-----------------------|----------------------------------------------------|
| Capacitance           | 100 uF                                             |
| Capacitance Tolerance | 20%                                                |
| Voltage DC            | 10 VDC (85C), 6.7 VDC (125C)                       |
| Temperature Range     | -55/+125°C                                         |
| Rated Temperature     | 85°C                                               |
| Dissipation Factor    | 8%                                                 |
| Failure Rate          | N/A                                                |
| Resistance            | 0.15 Ohms (100kHz)                                 |
| Ripple Current        | 860 mAmps (25C), 774 mAmps (85C), 344 mAmps (125C) |
| Leakage Current       | 10 uA                                              |

| Dimensions |                |
|------------|----------------|
| Footprint  | 7343           |
| L          | 7.3mm +/-0.3mm |
| W          | 4.3mm +/-0.3mm |
| H          | 1.5mm MAX      |
| S          | 1.3mm +/-0.3mm |
| F          | 2.4mm +/-0.1mm |
| K          | 1.3mm TYP      |

| Packaging Specifications |            |
|--------------------------|------------|
| Packaging                | T&R, 330mm |
| Packaging Quantity       | 4750       |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.