



RoHS+REACH

	PART NAME	MATERIALS	DESCRIPTION	REMARK	QTY.
1	HOUSING	NYLON UL94-V0	—————	NATURAL	1
2	CAP	LCP UL94-V0	—————	NATURAL	1
3	CONTACT PIN	PHOSPHOR BRONZE	G/F	—————	N
4	SOLDER TAB	BRASS	TIN-PLATED	—————	2



NOTES:

- ALL MATERIAL MUST BE COMPLY RoHS+REACH.
- SPECIALITY:
 - RATED VOLTAGE: 50V AC/DC
 - RATED CURRENT: 1A AC/DC (AWG.#28)
 - CONTACT RESISTANCE: 30 MILLIOHM MAX.
 - DIELECTRIC STRENGTH: 500V AC FOR 1 MINUTE BETWEEN ADJACENT TERMINAL, NO BREAKDOWN
 - INSULATION RESISTANCE: 100 MEGOHMS MIN.
 - OPERATING TEMPERATURE: -25°C to +85°C
- PART NO: 1WFO2-424XXX-00001

CODE
XXX: XX POSITIONS



POLES	DIM A	DIM B	POLES	DIM A	DIM B
2*4P	3.00	7.00	2*15P	14.00	18.00
2*5P	4.00	8.00	2*16P	15.00	19.00
2*6P	5.00	9.00	2*17P	16.00	20.00
2*7P	6.00	10.00	2*18P	17.00	21.00
2*8P	7.00	11.00	2*19P	18.00	22.00
2*9P	8.00	12.00	2*20P	19.00	23.00
2*10P	9.00	13.00	2*21P	20.00	24.00
2*11P	10.00	14.00	2*22P	21.00	25.00
2*12P	11.00	15.00	2*23P	22.00	26.00
2*13P	12.00	16.00	2*24P	23.00	27.00
2*14P	13.00	17.00	2*25P	24.00	28.00

5.0				DRAWING:	GENERAL TOLERANCE .X:=±0.30 .X°:=±2° .XX:=±0.20 .XX°:=±1° .XXX:=±0.10 .XXX°:=±0.5°
4.0				ZM	
3.0				CHECKED:	UNIT: MM PROJECTION: SCALE: 1/1 SHEET: 1/1
2.0					
1.0	22.06.02	NEW	ZM	APPROVAL:	
REV.	DATE	DESCRIPTION	DRAWING		

HIN-BAN
Electronic Technology

DESCRIPTION:	PH1.0 dual row vertical SMT Type with lock connector	
PART NO:	1WFO2-424XXX-00001	REV: 1.0
DRAWING NO:	UK0531	SIZE: A4