

Johanson Company: Johanson Technology inc. Product Release Date: 18 January, 2006

Deprecated P/N: 102S42E150FV4E

Web Page Link:

<https://www.johansontechnology.com/S42E>

Datasheet Date: 01-18-2024

Size for Capacitors (EIA): 1111

Description: Capacitors High-Q MLC E-Series,
1111, Hi-Q NP0/C0G, 1000V, 15pF \pm 1%, Ni/Sn
(RoHS), 7" Reel Embossed Tape

Specification Number: 35S0144B

Life Cycle Stage: Active - Production

Thickness (Max): 0.102

Schedule B: 8532

End Band (Min):

ECCN: EAR99

End Band (Max):

RoHS Compliance: Yes, RoHS 10/10

Standard Item: 1

REACH: 1

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important
to obtain a quotation with lead time for
production planning purposes. 12

Country of Origin: US

Length (Min): 0.100

Product Family: Capacitors

Length (Max): 0.130

Product Subfamily: Capacitors High-Q MLC E-
Series

Width (Min): 0.095

Capacitance Value: 15.000

Width (Max): 0.125

Cap Unit of Meas: pF

Packaged Weight (lb) Arm: 0.45

Tolerance: \pm 1%

Packaging: 7" Reel Embossed Tape

Voltage: 1000.0

Packaging Qty: 2000

Dielectric Temp Coefficient: Hi-Q NP0/C0G

Operating Temp Range: -55°C to +150°C

Termination: 68

Storage Temp Range (Packaged): -65°C to
+150°C

Marking: No Mark

Storage Temp Range (Non Operating): +5°C to
+40°C with RH 20% to 70%