



### General Information

Series	B45196P
Dielectric	MnO2 Tantalum
Style	SMD Chip
Description	SMD, Molded, High Temperature
Features	High Temperature
RoHS	Yes
Termination	Tin
AEC-Q200	No
Notes	Obsolete. Old Part Number [Obsolete] Was B45196P6335M306.

### Specifications

Capacitance	3.3 uF
Capacitance Tolerance	20%
Voltage DC	35 VDC (85C), 27.89 VDC (125C), 23.45 VDC (150C)
Temperature Range	-55/+150°C
Rated Temperature	85°C
Dissipation Factor	4.5%
Failure Rate	N/A
Resistance	1.7 Ohms (100kHz)
Leakage Current	1.2 uA

### Dimensions

Footprint	6032
L	6mm +/-0.3mm
W	3.2mm +/-0.3mm
H	2.5mm +/-0.3mm
S	1.3mm +/-0.3mm
F	2.2mm +/-0.1mm
K	1.8mm TYP

### Packaging Specifications

Packaging	T&R, 330mm
Packaging Quantity	3000