


Features

- NPN Complements to GSBCX54,GSBCX55,GSBCX56
- Low voltage
- High current

Applications

- Medium power general purposes
- Driver stages of audio amplifiers



SOT-89-3L

1. BASE
2. COLLECTOR
3. EMITTER

Absolute Maximum Ratings (T_A=25°C unless otherwise noted)

Parameter		Symbol	Value	Unit
Collector-Base Voltage	GSBCX51	V _{CBO}	-45	V
	GSBCX52		-60	
	GSBCX53		-100	
Collector-Emitter Voltage	GSBCX51	V _{CEO}	-45	V
	GSBCX52		-60	
	GSBCX53		-80	
Emitter-Base Voltage		V _{EBO}	-5	V
Collector Current		I _C	-1	A
Collector Power Dissipation		P _C	500	mW
Thermal Resistance From Junction To Ambient		R _{θJA}	250	°C/W
Junction Temperature		T _J	150	°C
Storage Temperature		T _{STG}	-55 to +150	°C

Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise noted)







Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit	
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C=-100\mu\text{A}, I_E=0$	GSBCX51	-45	-	-	V
			GSBCX52	-60	-	-	
			GSBCX53	-100	-	-	
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}^*$	$I_C=-10\text{mA}, I_B=0$	GSBCX51	-45	-	-	V
			GSBCX52	-60	-	-	
			GSBCX53	-80	-	-	
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E=-100\mu\text{A}, I_C=0$	-5	-	-	V	
Collector Cut-Off Current	I_{CBO}	$V_{CB}=-30\text{V}, I_E=0$	-	-	-0.1	μA	
Emitter Cut-Off Current	I_{EBO}	$V_{EB}=-5\text{V}, I_C=0$	-	-	-0.1	μA	
DC Current Gain	$h_{FE(1)}^*$	$V_{CE}=-2\text{V}, I_C=-5\text{mA}$	63	-	-	-	
	$h_{FE(2)}^*$	$V_{CE}=-2\text{V}, I_C=-150\text{mA}$	63	-	250	-	
	$h_{FE(3)}^*$	$V_{CE}=-2\text{V}, I_C=-0.5\text{A}$	40	-	-	-	
Collector-Emitter Saturation Voltage	$V_{CE(sat)}^*$	$I_C=-0.5\text{A}, I_B=-50\text{mA}$	-	-	-0.5	V	
Base -Emitter Voltage	V_{BE}^*	$V_{CE}=-2\text{V}, I_C=-0.5\text{A}$	-	-	-1	V	
Transition Frequency	f_T	$V_{CE}=-5\text{V}, I_C=-10\text{mA}$ $f=100\text{MHz}$	-	50	-	MHz	

* Pulse Test



Classification of $h_{FE(2)}$

Rank	GSBCX51	GSBCX51-10	GSBCX51-16
	GSBCX52	GSBCX52-10	GSBCX52-16
	GSBCX53	GSBCX53-10	GSBCX53-16
Range	63–250	63–160	100–250


Typical Electrical Characteristic Curves



Typical Electrical Characteristic Curves




Package Outline Dimensions SOT-89-3L



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.400	1.600	0.055	0.063
b	0.320	0.520	0.013	0.020
b1	0.400	0.580	0.016	0.023
c	0.350	0.440	0.014	0.017
D	4.400	4.600	0.173	0.181
D1	1.550 REF.		0.061 REF.	
E	2.300	2.600	0.091	0.102
E1	3.940	4.250	0.155	0.167
e	1.500 TYP.		0.060 TYP.	
e1	3.000 TYP.		0.118 TYP.	
L	0.900	1.200	0.035	0.047

Suggested Pad Layout



Note:

1. Controlling dimension: in millimeters.
2. General tolerance: ± 0.05 mm.
3. The pad layout is for reference purposes only.

Marking and Ordering Information

Device	Package	Marking	Quality	HSF Status
GSBCX51	SOT-89-3L	AA	1000pcs/Reel	RoHS Compliant
GSBCX51-10	SOT-89-3L	AC	1000pcs/Reel	RoHS Compliant
GSBCX51-16	SOT-89-3L	AD	1000pcs/Reel	RoHS Compliant
GSBCX52	SOT-89-3L	AE	1000pcs/Reel	RoHS Compliant
GSBCX52-10	SOT-89-3L	AG	1000pcs/Reel	RoHS Compliant
GSBCX52-16	SOT-89-3L	AM	1000pcs/Reel	RoHS Compliant
GSBCX53	SOT-89-3L	AH	1000pcs/Reel	RoHS Compliant
GSBCX53-10	SOT-89-3L	AK	1000pcs/Reel	RoHS Compliant
GSBCX53-16	SOT-89-3L	AL	1000pcs/Reel	RoHS Compliant