

FLORENTINA-2X2-SS

~16° smooth spot beam

SPECIFICATION:

Dimensions	89.7 x 89.7 mm
Height	29.7 mm
Fastening	pin, screw
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish
ROSE-CMC-SS	Single lens	PC	clear	
FLORENTINA-2X2-HLD	Holder	PC	black	

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
FCP14964_FLORENTINA-2X2-SS	Single lens	88	24	8	4.3
» Box size: 476 x 273 x 292 mm					






See also our general installation guide: www.ledil.com/installation_guide



OPTICAL RESULTS (MEASURED):





LED EASY-T FLUX 2x2 FLR XG xxx G7
 FWHM / FWTM 18.0° / 33.0°
 Efficiency 85 %
 Peak intensity 6.6 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:





LED EASY-T FLUX 2x2 FLR XT xxx G5
 FWHM / FWTM 17.0° / 31.0°
 Efficiency 86 %
 Peak intensity 7.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED XHP35 HD
 FWHM / FWTM 21.0° / 40.0°
 Efficiency 82 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14734_FLORENTINA-2X2-SHD



LED XHP35 HD
 FWHM / FWTM 21.0° / 40.0°
 Efficiency 82 %
 Peak intensity 4.7 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15196_FLORENTINA-2X2-SHD-OPEN



OPTICAL RESULTS (MEASURED):





LED XP-L HD
 FWHM / FWTM 20.0° / 37.0°
 Efficiency 79 %
 Peak intensity 5.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14960_FLORENTINA-2X2-SHD-WHT





LED XP-L HD
 FWHM / FWTM 20.0° / 37.0°
 Efficiency 79 %
 Peak intensity 5.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15196_FLORENTINA-2X2-SHD-OPEN



LED XP-L HD
 FWHM / FWTM 20.0° / 37.0°
 Efficiency 79 %
 Peak intensity 5.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14734_FLORENTINA-2X2-SHD




LED LUXEON MZ
 FWHM / FWTM 20.0° / 35.0°
 Efficiency 80 %
 Peak intensity 5.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14734_FLORENTINA-2X2-SHD





OPTICAL RESULTS (MEASURED):





LED LUXEON MZ
 FWHM / FWTM 20.0° / 35.0°
 Efficiency 80 %
 Peak intensity 5.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15196_FLORENTINA-2X2-SHD-OPEN





LED LUXEON MZ
 FWHM / FWTM 20.0° / 35.0°
 Efficiency 82 %
 Peak intensity 5.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14960_FLORENTINA-2X2-SHD-WHT



LED OSLON Square CSSRM2/CSSRM3
 FWHM / FWTM 16.0° / 30.0°
 Efficiency 82 %
 Peak intensity 7.7 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14960_FLORENTINA-2X2-SHD-WHT



LED OSLON Square CSSRM2/CSSRM3
 FWHM / FWTM 16.0° / 30.0°
 Efficiency 78 %
 Peak intensity 7.7 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14734_FLORENTINA-2X2-SHD





OPTICAL RESULTS (MEASURED):

OSRAM

Opto Semiconductors

LED OSLON Square EC
 FWHM / FWTM 17.0° / 31.0°
 Efficiency 83 %
 Peak intensity 7.6 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14734_FLORENTINA-2X2-SHD



OSRAM

Opto Semiconductors

LED OSLON Square EC
 FWHM / FWTM 17.0° / 31.0°
 Efficiency 83 %
 Peak intensity 7.6 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15196_FLORENTINA-2X2-SHD-OPEN

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)