

FLORENTINA-4X1-O

~45° + 15° oval beam

SPECIFICATION:

Dimensions	169.7 x 49.7 mm
Height	28.5 mm
Fastening	pin
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish
ROSE-CMC-O	Single lens	PC	clear	
FLORENTINA-4X1-HLD	Holder	PC	black	

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
FCP15347_FLORENTINA-4X1-O	Single lens	72	72	8	3.4
» Box size: 476 x 273 x 292 mm					






See also our general installation guide: www.ledil.com/installation_guide



OPTICAL RESULTS (MEASURED):



LED EASY-T FLUX 1x4 FLR XG xxx G7
 FWHM / FWTM 43.0 + 16.0° / 70.0 + 33.0°
 Efficiency 75 %
 Peak intensity 2.8 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15028_FLORENTINA-4X1-SHD





LED EASY-T FLUX 1x4 FLR XT xxx G5
 FWHM / FWTM 44.0 + 16.0° / 71.0 + 32.0°
 Efficiency 72 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15028_FLORENTINA-4X1-SHD



LED XP-G2
 FWHM / FWTM 41.0 + 17.0° / 102.0°
 Efficiency 71 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15198_FLORENTINA-4X1-SHD-OPEN





LED XP-G2
 FWHM / FWTM 41.0 + 17.0° / 70.0 + 32.0°
 Efficiency 71 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15028_FLORENTINA-4X1-SHD





OPTICAL RESULTS (MEASURED):





LED XP-L2
 FWHM / FWTM 43.0 + 19.0° / 70.0 + 40.0°
 Efficiency 72 %
 Peak intensity 2.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15028_FLORENTINA-4X1-SHD





LED XP-L2
 FWHM / FWTM 42.0 + 19.0° / 70.0 + 40.0°
 Efficiency 72 %
 Peak intensity 2.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15198_FLORENTINA-4X1-SHD-OPEN



LED XP-L2
 FWHM / FWTM 43.0 + 19.0° / 71.0 + 40.0°
 Efficiency 76 %
 Peak intensity 2.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15690_FLORENTINA-4X1-SHD-WHT





LED NVSxx19B/NVSxx19C
 FWHM / FWTM 44.0 + 16.0° / 70.0 + 31.0°
 Efficiency 75 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15198_FLORENTINA-4X1-SHD-OPEN





OPTICAL RESULTS (MEASURED):





LED NVSxx19B/NVSxx19C
 FWHM / FWTM 44.0 + 16.0° / 70.0 + 31.0°
 Efficiency 79 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15028_FLORENTINA-4X1-SHD





LED NVSxx19B/NVSxx19C
 FWHM / FWTM 44.0 + 16.0° / 71.0 + 31.0°
 Efficiency 78 %
 Peak intensity 2.9 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15690_FLORENTINA-4X1-SHD-WHT



LED OSLOM Square CSSRM2/CSSRM3
 FWHM / FWTM 44.0 + 15.0° / 70.0 + 30.0°
 Efficiency 74 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15028_FLORENTINA-4X1-SHD




LED OSLOM Square CSSRM2/CSSRM3
 FWHM / FWTM 44.0 + 15.0° / 69.0 + 30.0°
 Efficiency 69 %
 Peak intensity 3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C15198_FLORENTINA-4X1-SHD-OPEN



OPTICAL RESULTS (SIMULATED):



LED	XP-L HD
FWHM / FWTM	10.0 + 25.0° / 20.0 + 45.0°
Efficiency	198 %
Peak intensity	2.5 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	
	C15028_FLORENTINA-4X1-SHD



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)