

## OLGA-O

~20° + 40° oval beam

### SPECIFICATION:

Dimensions	Ø 29.7 mm
Height	18.3 mm
ROHS compliant	yes ⓘ


### MATERIALS:

Component	Type	Material	Colour	Finish
OLGA-O	Single lens	PMMA	clear	



### ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C16673_OLGA-O » Box size: 476 x 273 x 292 mm	792	132	66	7.2




See also our general installation guide: [www.ledil.com/installation\\_guide](http://www.ledil.com/installation_guide)

### OPTICAL RESULTS (MEASURED):




LED Vesta TW 6mm DP  
FWHM / FWTM 45.0 + 23.0° / 82.0 + 67.0°  
Efficiency 81 %  
Peak intensity 1.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




### CITIZEN

LED CLU7B2  
FWHM / FWTM 44.0 + 20.0° / 72.0 + 48.0°  
Efficiency 80 %  
Peak intensity 2.2 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:





### CITIZEN

LED CLU7L3  
FWHM / FWTM 43.0 + 19.0° / 71.0 + 45.0°  
Efficiency 83 %  
Peak intensity 2.5 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



### CITIZEN



LED CLU7R3  
FWHM / FWTM 44.0 + 22.0° / 74.0 + 55.0°  
Efficiency 80 %  
Peak intensity 2 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



## OPTICAL RESULTS (MEASURED):

### CITIZEN


LED CLU7S3  
 FWHM / FWTM 43.0 + 21.0° / 72.0 + 50.0°  
 Efficiency 88 %  
 Peak intensity 2.4 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:



### OPTICAL RESULTS (SIMULATED):




LED V6 HD Gen 7  
FWHM / FWTM 42.0 + 22.0° / 73.0 + 54.0°  
Efficiency 90 %  
Peak intensity 2.3 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



### CITIZEN


LED CLU7A2/7A3  
FWHM / FWTM 15.0 + 41.0°  
Efficiency 89 %  
LEDs/each optic 1  
Light colour White  
Required components:



LED CXA/B 13xx  
FWHM / FWTM 20.0 + 41.0°  
Efficiency 85 %  
LEDs/each optic 1  
Light colour White  
Required components:




LED CXM-3  
FWHM / FWTM 42.0 + 15.0° / 65.0 + 34.0°  
Efficiency 94 %  
Peak intensity 3.9 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



## OPTICAL RESULTS (SIMULATED):



LED	CXM-4
FWHM / FWTM	42.0 + 18.0° / 69.0 + 44.0°
Efficiency	93 %
Peak intensity	3 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	



### GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

### MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 13  
FI-24240 SALO  
Finland

#### LEDiL Inc.

228 West Page Street  
Suite D  
Sycamore IL 60178  
USA

#### Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B  
Casic Motor Building  
Shenzhen 518057  
P.R.CHINA

#### Local sales and technical support

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

#### Shipping locations

Salo, Finland  
Hong Kong, China

#### Distribution Partners

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)