

TINA-Y-SS

~16° smooth spot beam. Assembly with holder, installation tape and pins.



SPECIFICATION:

Dimensions	Ø 16.1 mm
Height	10 mm
Fastening	tape, pin
ROHS compliant	yes 


LEDiL®

MATERIALS:

Component	Type	Material	Colour	Finish
TINA-Y-SS	Single lens	PMMA	clear	gloss
TINA-Y-HLD	Holder	PC	black	gloss
TINA-Y-TAPE	Tape	Acrylic foam		

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
CA18103_TINA-Y-SS » Box size: 476 x 273 x 197 mm	3900	300	300	5.7





See also our general installation guide: www.ledil.com/installation_guide


OPTICAL RESULTS (MEASURED):




LED XP-G3
FWHM / FWTM 18.0° / 37.0°
Efficiency 81 %
Peak intensity 5.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED XP-G4
FWHM / FWTM 17.0° / 33.0°
Efficiency 87 %
Peak intensity 7.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED NVSW719AC
FWHM / FWTM 17.0° / 31.0°
Efficiency 87 %
Peak intensity 7.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED OSCONIQ C 3030
FWHM / FWTM 16.0° / 36.0°
Efficiency 83 %
Peak intensity 6.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:






OPTICAL RESULTS (SIMULATED):




LED	CLR6A-TKW
FWHM / FWTM	21.0° / 42.0°
Efficiency	86 %
Peak intensity	4.5 cd/lm
LEDs/each optic	1
Light colour	RGBW

Required components:




LED	XD16 Premium
FWHM / FWTM	14.0° / 26.0°
Efficiency	86 %
Peak intensity	11.4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LED	XE-G
FWHM / FWTM	16.0° / 28.0°
Efficiency	87 %
Peak intensity	9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LED	XHP35.2 HD
FWHM / FWTM	28.0° / 52.0°
Efficiency	75 %
Peak intensity	2.5 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




OPTICAL RESULTS (SIMULATED):




LED	XHP35.2 HI
FWHM / FWTM	22.0° / 46.0°
Efficiency	83 %
Peak intensity	3.8 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LED	XHP50.3 HI
FWHM / FWTM	24.0° / 48.0°
Efficiency	82 %
Peak intensity	3.4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LED	XM-L RGBW (XMLDCL HD)
FWHM / FWTM	30.0° / 50.0°
Efficiency	85 %
Peak intensity	2.7 cd/lm
LEDs/each optic	1
Light colour	RGBW

Required components:



LED	XM-L RGBW (XMLDCL HI)
FWHM / FWTM	20.0° / 38.0°
Efficiency	85 %
Peak intensity	5.3 cd/lm
LEDs/each optic	1
Light colour	RGBW

Required components:




OPTICAL RESULTS (SIMULATED):




LED	XM-L3
FWHM / FWTM	21.0° / 42.0°
Efficiency	80 %
Peak intensity	4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LED	XP-E2
FWHM / FWTM	12.0° / 24.0°
Efficiency	88 %
Peak intensity	13 cd/lm
LEDs/each optic	1
Light colour	White

Required components:




LED	XP-G2
FWHM / FWTM	15.0° / 28.0°
Efficiency	87 %
Peak intensity	9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:



LED	XP-P
FWHM / FWTM	12.0° / 22.0°
Efficiency	89 %
Peak intensity	15.1 cd/lm
LEDs/each optic	1
Light colour	White


Required components:




OPTICAL RESULTS (SIMULATED):




LED XQ-E HD
FWHM / FWTM 12.0° / 24.0°
Efficiency 87 %
Peak intensity 12.7 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED XQ-E HI
FWHM / FWTM 12.0° / 22.0°
Efficiency 87 %
Peak intensity 15.2 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED LUXEON 5050 Round LES
FWHM / FWTM 28.0° / 56.0°
Efficiency 80 %
Peak intensity 2.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED LUXEON 5050 Square LES
FWHM / FWTM 26.0° / 56.0°
Efficiency 78 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (SIMULATED):

LUMILEDS

LED	LUXEON C
FWHM / FWTM	14.0° / 26.0°
Efficiency	79 %
Peak intensity	10.8 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



LUMILEDS

LED	LUXEON MZ
FWHM / FWTM	24.0° / 47.0°
Efficiency	81 %
Peak intensity	3.4 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



LUMILEDS

LED	LUXEON TX
FWHM / FWTM	15.0° / 30.0°
Efficiency	84 %
Peak intensity	8 cd/lm
LEDs/each optic	1
Light colour	White


Required components:



NICHIA

LED	NV4WB35AM
FWHM / FWTM	24.0° / 46.0°
Efficiency	85 %
Peak intensity	3.7 cd/lm
LEDs/each optic	1
Light colour	White


Required components:




OPTICAL RESULTS (SIMULATED):




LED NVSW219F
FWHM / FWTM 18.0° / 33.0°
Efficiency 87 %
Peak intensity 6.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED NVSxE21A
FWHM / FWTM 16.0° / 34.0°
Efficiency 79 %
Peak intensity 7 cd/lm
LEDs/each optic 1
Light colour White
Required components:



Opto Semiconductors
LED OSLON Square CSSRM2/CSSRM3
FWHM / FWTM 16.0° / 32.0°
Efficiency 86 %
Peak intensity 7.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



Opto Semiconductors
LED OSLON SSL 150
FWHM / FWTM 13.0° / 25.0°
Efficiency 88 %
Peak intensity 13 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (SIMULATED):

OSRAM

Opto Semiconductors



LED SFH 4715AS
FWHM / FWTM 16.0° / 33.0°
Efficiency 86 %
LEDs/each optic 1
Light colour IR
Required components:



OSRAM


Opto Semiconductors

LED SFH 4725AS
FWHM / FWTM 16.0° / 34.0°
Efficiency 86 %
LEDs/each optic 1
Light colour IR
Required components:



SAMSUNG

LED LH351C
FWHM / FWTM 19.0° / 36.0°
Efficiency 87 %
Peak intensity 5.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations
Salo, Finland
Hong Kong, China

Distribution Partners
[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)