

MOLLY-W-B

~60° wide beam compatible with 3rd party connectors from BJB, Stucchi and Tridonic

SPECIFICATION:

Dimensions	Ø 69.8 mm
Height	22.1 mm
ROHS compliant	yes 




MATERIALS:

Component	Type	Material	Colour	Finish
MOLLY-W-B	Single lens	PMMA	clear	

ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C16265_MOLLY-W-B	180	36	18	7.5

» Box size: 480 x 280 x 300 mm



See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):

CITIZEN

LED CLL03x/CLU03x

FWHM / FWTM 62.0° / 86.0°

Efficiency 90 %



Peak intensity 0.9 cd/lm

LEDs/each optic 1

Light colour White

Required components:

BBJ: 47.319.2021



LUMILEDS

LED LUXEON CoB 1208

FWHM / FWTM 62.0° / 87.0°

Efficiency 91 %


Peak intensity 0.8 cd/lm

LEDs/each optic 1

Light colour White

Required components:

BBJ: 47.319.2011



TRIDONIC

LED SLE G7 LES15

FWHM / FWTM 63.0° / 88.0°

Efficiency 90 %



Peak intensity 0.8 cd/lm

LEDs/each optic 1

Light colour White

Required components:

BBJ: 47.319.2021



TRIDONIC

LED SLE G7 LES17 H

FWHM / FWTM 57.0° / 83.0°



Efficiency 89 %

Peak intensity 0.9 cd/lm

LEDs/each optic 1

Light colour White



Required components:



OPTICAL RESULTS (MEASURED):


TRIDONIC

LED SLE G7 LES21 H
FWHM / FWTM 58.0° / 85.0°
Efficiency 88 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour White
Required components:



XICATO

LED XOB 14.5 mm
FWHM / FWTM 62.0° / 88.0°
Efficiency 91 %
Peak intensity 0.8 cd/lm
LEDs/each optic 1
Light colour White
Required components:



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

**Ledil Optics Technology
(Shenzhen) Co., Ltd.**
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

**Local sales and technical
support**
www.ledil.com/
where_to_buy

Shipping locations
Salo, Finland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy