

STRADELLA-16-HB-W

~90° wide beam for industrial applications

SPECIFICATION:

Dimensions	49.5 x 49.5 mm
Height	7.1 mm
Fastening	pin, screw
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish
STRADELLA-16-HB-W	Multi-lens	PMMA	clear	



ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C15432_STRADELLA-16-HB-W » Box size: 480 x 280 x 300 mm	800	160	160	6.6





See also our general installation guide: www.ledil.com/installation_guide



OPTICAL RESULTS (MEASURED):





LED J Series 3030
FWHM / FWTM 86.0° / 125.0°
Efficiency 95 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED EHP-223.5x50-1604-xx-70-LS30-06-NTC
FWHM / FWTM 91.0° / 124.0°
Efficiency 96 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED NFSx757D
FWHM / FWTM 91.0° / 126.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED NFSx757G
FWHM / FWTM 92.0° / 121.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





OPTICAL RESULTS (MEASURED):




LED NVSW219D
FWHM / FWTM 87.0° / 125.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





LED NVSW319B
FWHM / FWTM 96.0° / 131.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED PrevaLED Brick MP 4x16
FWHM / FWTM 88.0° / 122.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED Duris S5 (2 chip)
FWHM / FWTM 87.0° / 125.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour Purple
Required components:




OPTICAL RESULTS (MEASURED):

OSRAM

Opto Semiconductors



LED Duris S5 (Single chip)
FWHM / FWTM 88.0° / 125.0°
Efficiency 93 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OSRAM



Opto Semiconductors

LED OSCONIQ S 3030 (QSLR31)
FWHM / FWTM 84.0° / 124.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





PHILIPS

LED Fortimo FastFlex LED 4x16 DHE G4
FWHM / FWTM 87.0° / 122.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



SAMSUNG



LED HiLOM RM64 (LM301B)
FWHM / FWTM 88.0° / 123.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OPTICAL RESULTS (MEASURED):



SAMSUNG

LED LM231 A/B
FWHM / FWTM 88.0° / 126.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





SCIOLUX

LED XLE-S44XTEHE (XT-E HE)
FWHM / FWTM 88.0° / 133.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:




SCIOLUX

LED XLE-S48XPG3 (XP-G3)
FWHM / FWTM 100.0° / 134.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:











SEOUL SEMICONDUCTOR

LED SEOUL 3030
FWHM / FWTM 87.0° / 125.0°
Efficiency 93 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (MEASURED):

<p>SEOUL SEMICONDUCTOR</p> <p>LED: SEOUL DC 3030</p> <p>FWHM / FWTM: 90.0° / 129.0°</p> <p>Efficiency: 94 %</p> <p>Peak intensity: 0.5 cd/lm</p> <p>LEDs/each optic: 1</p> <p>Light colour: White</p> <p>Required components:</p>		
<p>SEOUL SEMICONDUCTOR</p> <p>LED: Z5M3</p> <p>FWHM / FWTM: 93.0° / 132.0°</p> <p>Efficiency: 94 %</p> <p>Peak intensity: 0.5 cd/lm</p> <p>LEDs/each optic: 1</p> <p>Light colour: White</p> <p>Required components:</p>		
<p>TRIDONIC</p> <p>LED: RLE 4x16 4000lm MP ADV2 OTD</p> <p>FWHM / FWTM: 88.0° / 123.0°</p> <p>Efficiency: 94 %</p> <p>Peak intensity: 0.5 cd/lm</p> <p>LEDs/each optic: 1</p> <p>Light colour: White</p> <p>Required components:</p>		
<p>TRIDONIC</p> <p>LED: RLE 4x8 2000lm MP ADV2 OTD</p> <p>FWHM / FWTM: 88.0° / 123.0°</p> <p>Efficiency: 94 %</p> <p>Peak intensity: 0.5 cd/lm</p> <p>LEDs/each optic: 1</p> <p>Light colour: White</p> <p>Required components:</p>		

OPTICAL RESULTS (SIMULATED):




LED CSP 2727 (BXCP)
 FWHM / FWTM 98.0° / 116.0°
 Efficiency 96 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED CSP 2727 (BXCP)
 FWHM / FWTM 97.0° / 118.0°
 Efficiency 87 %
 Peak intensity 0.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:


Protective plate, glass



LED J Series 5050 Round LES
 FWHM / FWTM 85.0° / 121.0°
 Efficiency 96 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED XP-G2 HE
 FWHM / FWTM 91.0° / 128.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




OPTICAL RESULTS (SIMULATED):




LED XT-E
FWHM / FWTM 99.0° / 126.0°
Efficiency 93 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED LUXEON 5050 Square LES
FWHM / FWTM 83.0° / 121.0°
Efficiency 96 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:



LED LUXEON HL1Z
FWHM / FWTM 106.0° / 118.0°
Efficiency 95 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:




LED NVSW519A
FWHM / FWTM 99.0° / 126.0°
Efficiency 93 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (SIMULATED):




LED NVSxE21A
 FWHM / FWTM 98.0° / 121.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED Duris E5
 FWHM / FWTM 87.0° / 123.0°
 Efficiency 94 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:




LED OSCONIQ C 2424
 FWHM / FWTM 94.0° / 122.0°
 Efficiency 96 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:



LED OSCONIQ C 3030
 FWHM / FWTM 90.0° / 120.0°
 Efficiency 88 %
 Peak intensity 0.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:

Protective plate, glass




OPTICAL RESULTS (SIMULATED):

OSRAM

Opto Semiconductors


LED OSCONIQ C 3030
FWHM / FWTM 92.0 + 90.0° / 120.0°
Efficiency 96 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OSRAM

Opto Semiconductors


LED OSCONIQ P 3030
FWHM / FWTM 79.0° / 128.0°
Efficiency 97 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OSRAM

Opto Semiconductors


LED OSCONIQ P 3737 (3W version)
FWHM / FWTM 88.0 + 87.0° / 124.0°
Efficiency 96 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OSRAM

Opto Semiconductors

LED OSLON Square CSSRM2/CSSRM3
FWHM / FWTM 97.0° / 124.0°
Efficiency 94 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour Red
Required components:




OPTICAL RESULTS (SIMULATED):

OSRAM


Opto Semiconductors

LED SFH 4715AS
FWHM / FWTM 66.0° / 106.0°
Efficiency 96 %
Peak intensity 0.8 cd/lm
LEDs/each optic 1
Light colour IR
Required components:



SAMSUNG


LED LH231B
FWHM / FWTM 92.0° / 118.0°
Efficiency 95 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



SAMSUNG


LED LH231B
FWHM / FWTM 92.0° / 118.0°
Efficiency 87 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:

Protective plate, glass



SAMSUNG

LED LH351C
FWHM / FWTM 97.0° / 124.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:




OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LM301B
FWHM / FWTM 113.0° / 133.0°
Efficiency 96 %
Peak intensity 0.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:

Protective plate, glass




SAMSUNG

LED LM301B
FWHM / FWTM 90.0° / 125.0°
Efficiency 94 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:




SAMSUNG

LED LM302D
FWHM / FWTM 90.0° / 124.0°
Efficiency 96 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:





SEOUL SEMICONDUCTOR

LED SEOUL DC 3030C
FWHM / FWTM 91.0° / 124.0°
Efficiency 96 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:



OPTICAL RESULTS (SIMULATED):

<p>SEOUL SEMICONDUCTOR</p> <p>LED: SEOUL DC 5050 6V</p> <p>FWHM / FWTM: 84.0° / 122.0°</p> <p>Efficiency: 94 %</p> <p>Peak intensity: 0.6 cd/lm</p> <p>LEDs/each optic: 1</p> <p>Light colour: White</p> <p>Required components:</p>	
<p>SEOUL SEMICONDUCTOR</p> <p>LED: Z8Y22T</p> <p>FWHM / FWTM: 94.0° / 124.0°</p> <p>Efficiency: 94 %</p> <p>Peak intensity: 0.5 cd/lm</p> <p>LEDs/each optic: 1</p> <p>Light colour: White</p> <p>Required components:</p>	

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)