

## HB-SQ-WWW

~90° beam. Assembly with installation tape.

## SPECIFICATION:


Dimensions	25.0 x 25.0 mm
Height	10 mm
Fastening	tape, pin
ROHS compliant	yes ⓘ

## MATERIALS:

Component	Type	Material	Colour	Finish
HB-SQ-WWW	Single lens	PMMA	clear	
ROSE-TAPE	Tape	Acrylic foam	black	

## ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CA16372_HB-SQ-WWW	Single lens	2058	294	98	8.9
» Box size: 480 x 280 x 300 mm					








### OPTICAL RESULTS (MEASURED):



LED XHP70  
FWHM / FWTM 88.0° / 122.0°  
Efficiency 91 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




LED LUXEON 5050 Round LES  
FWHM / FWTM 80.0° / 110.0°  
Efficiency 93 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




### OPTICAL RESULTS (SIMULATED):




LED Bridgelux SMD 5050  
FWHM / FWTM 77.0° / 108.0°  
Efficiency 93 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




LED MHD-E/G  
FWHM / FWTM 85.5° / 120.0°  
Efficiency 91 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



LED XHP50.2  
FWHM / FWTM 86.0° / 120.0°  
Efficiency 93 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




LED XHP70.2  
FWHM / FWTM 85.0° / 119.0 + 120.0°  
Efficiency 86 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



### OPTICAL RESULTS (SIMULATED):

#### LUMILEDS


LED LUXEON 7070  
FWHM / FWTM 74.0° / 108.0°  
Efficiency 92 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



#### LUMILEDS

LED LUXEON 7070  
FWHM / FWTM 75.0° / 108.0°  
Efficiency 83 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:


Protective plate, glass



#### LUMILEDS


LED LUXEON M/MX  
FWHM / FWTM 88.0° / 121.0°  
Efficiency 86 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:

Protective plate, glass



#### LUMILEDS


LED LUXEON M/MX  
FWHM / FWTM 80.0° / 109.0°  
Efficiency 90 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



### OPTICAL RESULTS (SIMULATED):


#### LUMILEDS

LED LUXEON MZ  
FWHM / FWTM 77.0° / 107.0°  
Efficiency 94 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




#### LUMILEDS

LED LUXEON V  
FWHM / FWTM 81.0° / 111.0°  
Efficiency 92 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




#### NICHIA

LED NV4x144A  
FWHM / FWTM 86.0° / 121.0°  
Efficiency 90 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:



#### OSRAM

Opto Semiconductors  
LED Duris S10  
FWHM / FWTM 74.0° / 107.0°  
Efficiency 95 %  
Peak intensity 0.6 cd/lm  
LEDs/each optic 1  
Light colour White  
Required components:




### OPTICAL RESULTS (SIMULATED):

#### OSRAM

Opto Semiconductors


LED OSCONIQ C 2424  
 FWHM / FWTM 74.0 + 73.0° / 104.0 + 105.0°  
 Efficiency 94 %  
 Peak intensity 0.7 cd/lm  
 LEDs/each optic 4  
 Light colour White  
 Required components:



#### OSRAM

Opto Semiconductors



LED OSCONIQ P 7070  
 FWHM / FWTM 75.0° / 105.0 + 103.0°  
 Efficiency 91 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 1  
 Light colour White  
 Required components:



#### OSRAM

Opto Semiconductors



LED SFH 4715AS  
 FWHM / FWTM 65.0° / 93.0°  
 Efficiency 94 %  
 LEDs/each optic 1  
 Light colour IR  
 Required components:



#### OSRAM

Opto Semiconductors


LED SFH 4716AS  
 FWHM / FWTM 76.0° / 100.0°  
 Efficiency 93 %  
 LEDs/each optic 1  
 Light colour IR  
 Required components:



### OPTICAL RESULTS (SIMULATED):

**OSRAM**  
Opto Semiconductors

LED SFH 4716S  
FWHM / FWTM 75.0° / 101.0°  
Efficiency 93 %  
LEDs/each optic 1  
Light colour IR  
Required components:



### GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

### MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 13  
FI-24240 SALO  
Finland

#### LEDiL Inc.

228 West Page Street  
Suite D  
Sycamore IL 60178  
USA

#### Ledil Optics Technology (Shenzhen) Co., Ltd.

# 405 , Block B  
Casic Motor Building  
Shenzhen 518057  
P.R.CHINA

#### Local sales and technical support

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)

#### Shipping locations

Salo, Finland  
Hong Kong, China

#### Distribution Partners

[www.ledil.com/  
where\\_to\\_buy](http://www.ledil.com/where_to_buy)