

Product data sheet

Specifications



Thermal overload relay, Easy TeSys DPER, 5.5-8A, class 10

DPER12

Main

Range	Easy TeSys
Product Name	Easy TeSys DPER
Product Or Component Type	Thermal overload relay
Device Short Name	DPER
Relay Application	Overload protection
Product Compatibility	Contactor DPE09-38
Thermal Protection Adjustment Range	5.5...8 A
Thermal Overload Class	Class 10 IEC 60947-4-1
[Ui] Rated Insulation Voltage	Power circuit 600 V cUL Power circuit 690 V IEC 60947-4-1

Complementary

Network Type	DC AC
Network Frequency	0...400 Hz
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A signalling circuit
Permissible Current	1.5 A 240 V AC-15 signalling circuit 0.1 A 250 V DC-13 signalling circuit
Phase Failure Sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0
Tripping Threshold	1.14 +/- 0.06 Ir IEC 60947-4-1
Protection Type	BS fuse 5 A control circuit GB2 circuit breaker 5 A control circuit GG fuse 5 A control circuit
[Ue] Rated Operational Voltage	690 V AC 0...400 Hz power circuit IEC 60947-4-1
[Uimp] Rated Impulse Withstand Voltage	6 kV
Surge Withstand	6 kV IEC 60801-5
Dielectric Strength	1.89 kV 50 Hz IEC 60947-1
Control Type	Red push-button stop Blue push-button reset
Mounting Support	Separate, with specific accessories Under contactor

Connections - Terminals	Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) flexible with cable end Control circuit screw clamp terminals 2 0.00...0.00 in ² (1...2.5 mm ²) solid without cable end Power circuit screw clamp terminals 1 0.00...0.01 in ² (1.5...6 mm ²) flexible without cable end Power circuit screw clamp terminals 1 0.00...0.01 in ² (1...4 mm ²) flexible with cable end Power circuit screw clamp terminals 1 0.00...0.01 in ² (1...6 mm ²) solid without cable end
Tightening Torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals
Height	2.60 in (66 mm)
Width	1.77 in (45 mm)
Depth	2.76 in (70 mm)
Net Weight	0.27 lb(US) (0.124 kg)

Environment

Ip Degree Of Protection	IP20 IEC 60529
Protective Treatment	TH IEC 60068
Temperature Compensation	-4...140 °F (-20...60 °C)
Ambient Air Temperature For Operation	-4...140 °F (-20...60 °C) without derating IEC 60947-4-1
Ambient Air Temperature For Storage	-76...158 °F (-60...70 °C)
Shock Resistance	15 gn 11 ms IEC 60068-2-7
Vibration Resistance	6 gn on plate IEC 60068-2-6
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 cUL
Product Certifications	cUL

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.97 in (5.0 cm)
Package 1 Width	3.03 in (7.7 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	5.15 oz (146.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	24
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	8.40 lb(US) (3.81 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	384

Package 3 Height	31.50 in (80.0 cm)
Package 3 Width	31.50 in (80.0 cm)
Package 3 Length	23.62 in (60.0 cm)
Package 3 Weight	153.31 lb(US) (69.54 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 RoHS Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu RoHS Directive Compliant with Exemptions

China RoHS Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)