

DAISY-7X1-M-D

~35° wide beam. Variant with diffused lenses.

SPECIFICATION:

Dimensions	279.5 x 39.6 mm
Height	20.3 mm
Fastening	pin, screw, clips
ROHS compliant	yes ⓘ

MATERIALS:





Component	Type	Material	Colour	Finish
C18143_DAISY-7X1-M-D	Linear lens	PMMA		
C18409_DAISY-7X1-SHD-MET-MATT	Shade	PC	metal	matt
C18167_DAISY-7X1-SHD-MET	Shade	PC	metal	gloss
C17225_DAISY-7X1-SHD-WHT-MATT	Shade	PC	white	matt
C17051_DAISY-7X1-SHD-MATT	Shade	PC	black	matt
C16876_DAISY-7X1-SHD-WHT	Shade	PC	white	gloss
C16872_DAISY-7X1-SHD	Shade	PC	black	gloss


ORDERING INFORMATION:

Quantities for one set:

Linear lens	1
Shade	1

Component		Qty in box	MOQ	MPQ	Box weight (kg)
C18143_DAISY-7X1-M-D » Box size: 400 x 300 x 300 mm	Linear lens	312	312	24	6.4
C16876_DAISY-7X1-SHD-WHT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.6
C18167_DAISY-7X1-SHD-MET » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.0
C17051_DAISY-7X1-SHD-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.3
C18409_DAISY-7X1-SHD-MET-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.0
C17225_DAISY-7X1-SHD-WHT-MATT » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.6
C16872_DAISY-7X1-SHD » Box size: 595 x 360 x 230 mm	Shade	156	312	24	7.1







See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):

MST



Your solutions

LED LinLED 280x28mm 1600lm 840 4C 21V DAISY 7x1(ZT25)
 FWHM / FWTM 35.0° / 77.0°
 Efficiency 74 %
 Peak intensity 1.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C16872_DAISY-7X1-SHD



NICHIA


LED NCSxE17A
 FWHM / FWTM 32.0° / 74.0°
 Efficiency 72 %
 Peak intensity 1.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C17051_DAISY-7X1-SHD-MATT



OPTICAL RESULTS (SIMULATED):


LUMILEDS

LED LUXEON 2835 Line
FWHM / FWTM 40.0° / 80.0°
Efficiency 77 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C16872_DAISY-7X1-SHD




LUMILEDS

LED LUXEON 2835 Line
FWHM / FWTM 43.0° / 88.0°
Efficiency 79 %
Peak intensity 1.1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C16872_DAISY-7X1-SHD




LUMILEDS

LED LUXEON 3020
FWHM / FWTM 37.0° / 76.0°
Efficiency 77 %
Peak intensity 1.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C16872_DAISY-7X1-SHD



NICHIA


LED NF2W757G-MT (Tunable White)
FWHM / FWTM 48.0° / 94.0°
Efficiency 75 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour Tunable White
Required components:
C17051_DAISY-7X1-SHD-MATT




OPTICAL RESULTS (SIMULATED):




LED NF2W757G-MT (Tunable White)
FWHM / FWTM 50.0° / 94.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour Tunable White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT




LED NF2W757G-MT (Tunable White)
FWHM / FWTM 50.0° / 94.0°
Efficiency 76 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour Tunable White
Required components:
C16872_DAISY-7X1-SHD



LED NF2W757G-MT (Tunable White)
FWHM / FWTM 48.0° / 94.0°
Efficiency 88 %
Peak intensity 1.1 cd/lm
LEDs/each optic 2
Light colour Tunable White
Required components:
C18167_DAISY-7X1-SHD-MET




LED NF2W757G-MT (Tunable White)
FWHM / FWTM 51.0° / 94.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour Tunable White
Required components:
C16876_DAISY-7X1-SHD-WHT




OPTICAL RESULTS (SIMULATED):




LED NF2W757G-MT (Tunable White)
FWHM / FWTM 48.0° / 92.0°
Efficiency 88 %
Peak intensity 1.1 cd/lm
LEDs/each optic 2
Light colour Tunable White
Required components:
C17533_DAISY-7X1-SHD-MET-MATT




LED NF2W757H
FWHM / FWTM 50.0° / 94.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C16876_DAISY-7X1-SHD-WHT



LED NF2W757H
FWHM / FWTM 50.0° / 94.0°
Efficiency 88 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17533_DAISY-7X1-SHD-MET-MATT




LED NF2W757H
FWHM / FWTM 50.0° / 94.0°
Efficiency 75 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17051_DAISY-7X1-SHD-MATT




OPTICAL RESULTS (SIMULATED):




LED NF2W757H
FWHM / FWTM 51.0° / 94.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT




LED NF2W757H
FWHM / FWTM 48.0° / 94.0°
Efficiency 76 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C16872_DAISY-7X1-SHD



LED NF2W757H
FWHM / FWTM 50.0° / 94.0°
Efficiency 88 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C18167_DAISY-7X1-SHD-MET




LED NF2x757G
FWHM / FWTM 50.0° / 94.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT




OPTICAL RESULTS (SIMULATED):




LED NF2x757G
FWHM / FWTM 48.0° / 93.0°
Efficiency 75 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C16872_DAISY-7X1-SHD




LED NF2x757G
FWHM / FWTM 50.0° / 94.0°
Efficiency 88 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C18167_DAISY-7X1-SHD-MET



LED NF2x757G
FWHM / FWTM 52.0° / 94.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C16876_DAISY-7X1-SHD-WHT




LED NF2x757G
FWHM / FWTM 50.0° / 94.0°
Efficiency 88 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17533_DAISY-7X1-SHD-MET-MATT




OPTICAL RESULTS (SIMULATED):




LED NF2x757G
FWHM / FWTM 50.0° / 94.0°
Efficiency 75 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17051_DAISY-7X1-SHD-MATT




LED NFSW757H
FWHM / FWTM 50.0° / 94.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17225_DAISY-7X1-SHD-WHT-MATT



LED NFSW757H
FWHM / FWTM 48.0° / 93.0°
Efficiency 76 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C16872_DAISY-7X1-SHD




LED NFSW757H
FWHM / FWTM 48.0° / 92.0°
Efficiency 88 %
Peak intensity 1.1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C18167_DAISY-7X1-SHD-MET




OPTICAL RESULTS (SIMULATED):




LED NFSW757H
FWHM / FWTM 50.0° / 94.0°
Efficiency 86 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C16876_DAISY-7X1-SHD-WHT




LED NFSW757H
FWHM / FWTM 50.0° / 94.0°
Efficiency 88 %
Peak intensity 1.1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17533_DAISY-7X1-SHD-MET-MATT



LED NFSW757H
FWHM / FWTM 50.0° / 94.0°
Efficiency 76 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17051_DAISY-7X1-SHD-MATT




LED LM28xB Series
FWHM / FWTM 40.0° / 82.0°
Efficiency 87 %
Peak intensity 1.4 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17051_DAISY-7X1-SHD-MATT



OPTICAL RESULTS (SIMULATED):


SAMSUNG

LED LM301Z Plus
FWHM / FWTM 48.0° / 92.0°
Efficiency 86 %
Peak intensity 1.1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17225_DAISSY-7X1-SHD-WHT-MATT




SAMSUNG

LED LM301Z Plus
FWHM / FWTM 50.0° / 92.0°
Efficiency 88 %
Peak intensity 1.1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C18167_DAISSY-7X1-SHD-MET



SAMSUNG

LED LM301Z Plus
FWHM / FWTM 48.0° / 92.0°
Efficiency 75 %
Peak intensity 1 cd/lm
LEDs/each optic 2
Light colour White
Required components:
C17051_DAISSY-7X1-SHD-MATT



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Salo, Finland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)