# **Product data sheet**

Specification





# Fuse carrier, TeSys DF, 3P, 32A, 690VAC, fuse size 10x38mm

DF103

#### Main

Range	TeSys
Product Name	TeSys DF
Product Or Component Type	Fuse carrier
Device Short Name	DF10
Product Compatibility	DF2CA fuse cartridge DF2CN fuse cartridge
Poles Description	3P
Fuse Size	10 x 38 mm
Fuse Type	, gG , aM
Control Type	Toggle padlockable
Utilisation Category	AC-20B IEC 60947-3 DC-20B IEC 60947-3
[Ue] Rated Operational Voltage	690 V AC 690 V DC
[le] Rated Operational Current	32 A 400 V AC
[Ith] Conventional Free Air Thermal Current	32 A 68 °F (20 °C)
[Ui] Rated Insulation Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	6 kV
Overvoltage Category	III
Short-Circuit Withstand	120 kA 400 V IEC 60947-3 120 kA 500 V IEC 60947-3
Power Dissipation In W	3 W maximum power dissipation by fuse

### Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1 EN 45545-2 R22 HL2
Product Certifications	IEC UL recognized CSA CCC EAC DNV-GL
Mounting Support	35 mm symmetrical DIN rail
Mounting Position	Vertical +/- 23°)

Connections - Terminals	screw clamp terminals 1 0.000.02 in² (116 mm²)rigid screw clamp terminals 2 0.000.01 in² (16 mm²)rigid screw clamp terminals 1 0.000.02 in² (116 mm²)flexible with or without screw clamp terminals 2 0.000.01 in² (16 mm²)flexible with or without	
Tightening Torque	19.47 lbf.in (2.2 N.m) PZ2 19.47 lbf.in (2.2 N.m) flat Ø 5.5 mm	
Height	3.13 in (79.5 mm)	
Width	2.07 in (52.5 mm)	
Depth	2.40 in (61 mm)	
Net Weight	0.28 lb(US) (0.126 kg)	
Quantity Per Set	Set of 4	

#### **Environment**

Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40…158 °F (-40…70 °C) with derating above 20°C
Operating Altitude	02000 m
Ip Degree Of Protection	IP20
Pollution Degree	3
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	DF10

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	2.09 in (5.300 cm)	
Package 1 Width	2.44 in (6.200 cm)	
Package 1 Length	3.15 in (8.000 cm)	
Package 1 Weight	4.69 oz (133.000 g)	
Unit Type Of Package 2	BB1	
Number Of Units In Package 2	4	
Package 2 Height	2.68 in (6.800 cm)	
Package 2 Width	3.35 in (8.500 cm)	
Package 2 Length	8.74 in (22.200 cm)	
Package 2 Weight	20.11 oz (570.000 g)	
Unit Type Of Package 3	S03	
Number Of Units In Package 3	64	
Package 3 Height	11.81 in (30.000 cm)	
Package 3 Width	11.81 in (30.000 cm)	
Package 3 Length	15.75 in (40.000 cm)	
ackage 3 Weight 20.95 lb(US) (9.504 kg)		

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations  End of Life Information