



Click [here](#) for the 3D model.

## Dimensions

D	75mm +/-0.5mm
L	247mm +/-2mm
W	21mm +/-1mm
S	35mm +/-1mm
W1	45mm +/-1mm

## Packaging Specifications

Mounting	Bolt - M12x16
Packaging	Bulk, Bag

## General Information

Series	C20A
Dielectric	Metallized Polypropylene
Style	Can
Features	Single Phase PFC
RoHS	With Exemptions
SCIP Number	2d92f699-4786-4192-9c9d-d5c4faebc1e6
Lead	Threaded Studs M10
AEC-Q200	No
Miscellaneous	Thermal Resistance = 5.3 C/W.
Notes	This part is Not For New Design. See part number C44PXGR5330RASK.

## Specifications

Capacitance	33 $\mu$ F
Capacitance Tolerance	10%
Voltage AC	1000 VAC
Voltage DC	2300 VDC
Temperature Range	-25/+70°C
Rated Temperature	70°C
Insulation Resistance	10 MOhms
Max dV/dt	85 V/us
Resistance	1.7 mOhms (10kHz)
Ripple Current	40 Amps (10kHz 40C)
Inductance	165 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute a warranty or we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended to be used only by customers who have the required experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.