




N-Channel Enhancement Mode Power MOSFET

| | | | |
|--|---|----------------|------------------|
| <p>Description</p> <p>The G08N02L uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge. It can be used in a wide variety of applications.</p> <p>General Features</p> <ul style="list-style-type: none"> ● V_{DS} 20V ● I_D (at $V_{GS} = 10V$) 8A ● $R_{DS(ON)}$ (at $V_{GS} = 4.5V$) < 12.3mΩ ● $R_{DS(ON)}$ (at $V_{GS} = 2.5V$) < 13.7mΩ ● 100% Avalanche Tested ● RoHS Compliant <p>Application</p> <ul style="list-style-type: none"> ● Power switch ● DC/DC converters |  <p>Schematic Diagram</p>  <p>Marking and pin assignment</p>  <p>SOT-23-3L</p> | | |
| Device | Package | Marking | Packaging |
| G08N02L | SOT-23-3L | G08N02 | 3000pcs/Reel |




| Absolute Maximum Ratings $T_C = 25^\circ\text{C}$, unless otherwise noted | | | |
|---|----------------|------------|--------------------|
| Parameter | Symbol | Value | Unit |
| Drain-Source Voltage | V_{DS} | 20 | V |
| Continuous Drain Current | I_D | 8 | A |
| Pulsed Drain Current (note1) | I_{DM} | 32 | A |
| Gate-Source Voltage | V_{GS} | ± 12 | V |
| Power Dissipation | P_D | 1.5 | W |
| Single pulse avalanche energy (note3) | E_{AS} | 64 | mJ |
| Operating Junction and Storage Temperature Range | T_J, T_{stg} | -55 To 150 | $^\circ\text{C}$ |
| Thermal Resistance | | | |
| Parameter | Symbol | Value | Unit |
| Thermal Resistance, Junction-to-Case | R_{thJC} | 83 | $^\circ\text{C/W}$ |

Specifications $T_J = 25^\circ\text{C}$, unless otherwise noted

| Parameter | Symbol | Test Conditions | Value | | | Unit |
|--|-----------------------------|--|-------|------|-----------|------------------|
| | | | Min. | Typ. | Max. | |
| Static Parameters | | | | | | |
| Drain-Source Breakdown Voltage | $V_{(\text{BR})\text{DSS}}$ | $V_{GS} = 0\text{V}, I_D = 250\mu\text{A}$ | 20 | -- | -- | V |
| Zero Gate Voltage Drain Current | I_{DSS} | $V_{DS} = 20\text{V}, V_{GS} = 0\text{V}$ | -- | -- | 1 | μA |
| Gate-Source Leakage | I_{GSS} | $V_{GS} = \pm 12\text{V}$ | -- | -- | ± 100 | nA |
| Gate-Source Threshold Voltage | $V_{GS(\text{th})}$ | $V_{DS} = V_{GS}, I_D = 250\mu\text{A}$ | 0.5 | 0.64 | 0.9 | V |
| Drain-Source On-Resistance | $R_{DS(\text{on})}$ | $V_{GS} = 4.5\text{V}, I_D = 12\text{A}$ | -- | 10 | 12.3 | $\text{m}\Omega$ |
| | | $V_{GS} = 2.5\text{V}, I_D = 12\text{A}$ | -- | 11 | 13.7 | |
| Forward Transconductance | g_{FS} | $V_{DS}=10\text{V}, I_D=4\text{A}$ | -- | 38 | -- | S |
| Dynamic Parameters | | | | | | |
| Input Capacitance | C_{iss} | $V_{GS} = 0\text{V}, V_{DS} = 10\text{V}, f = 1.0\text{MHz}$ | -- | 929 | -- | pF |
| Output Capacitance | C_{oss} | | -- | 163 | -- | |
| Reverse Transfer Capacitance | C_{rss} | | -- | 124 | -- | |
| Total Gate Charge | Q_g | $V_{DS} = 10\text{V}, I_D = 8\text{A}, V_{GS} = 10\text{V}$ | -- | 22 | -- | nC |
| Gate-Source Charge | Q_{gs} | | -- | 3.8 | -- | |
| Gate-Drain Charge | Q_{gd} | | -- | 4.6 | -- | |
| Turn-on Delay Time | $t_{d(\text{on})}$ | $V_{DD} = 10\text{V}, I_D = 5\text{A}, R_G = 50\Omega$ | -- | 320 | -- | ns |
| Turn-on Rise Time | t_r | | -- | 1100 | -- | |
| Turn-off Delay Time | $t_{d(\text{off})}$ | | -- | 4050 | -- | |
| Turn-off Fall Time | t_f | | -- | 2600 | -- | |
| Drain-Source Body Diode Characteristics | | | | | | |
| Continuous Body Diode Current | I_S | $T_C = 25^\circ\text{C}$ | -- | -- | 8 | A |
| Body Diode Voltage | V_{SD} | $T_J = 25^\circ\text{C}, I_{SD} = 1\text{A}, V_{GS} = 0\text{V}$ | -- | -- | 1.2 | V |

Notes

- Repetitive Rating: Pulse width limited by maximum junction temperature
- Identical low side and high side switch with identical R_G
- EAS condition : $T_J=25^\circ\text{C}$, $V_{DD}=20\text{V}$, $V_{GS}=10\text{V}$, $L=0.5\text{mH}$, $R_g=25\Omega$

Gate Charge Test Circuit**EAS Test Circuit****Switch Time Test Circuit**

Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. Gate Charge




Figure 4. Drain Source On Resistance




Figure 5. Capacitance vs Vds





Figure 6. Source-Drain Diode Forward



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 7. Drain-Source On-Resistance




Figure 8. Safe Operation Area






Figure 9. Normalized Maximum Transient Thermal Impedance



SOT-23-3L Package Information



| Symbol | Dimensions in Millimeters | | |
|----------------------|---------------------------|-------|-------|
| | MIN. | NOM. | MAX. |
| A | 2.80 | 2.90 | 3.00 |
| B | 1.50 | 1.60 | 1.70 |
| C | 1.00 | 1.10 | 1.20 |
| D | 0.30 | 0.40 | 0.50 |
| E | 0.25 | 0.40 | 0.55 |
| G | | 1.90 | |
| H | 0.00 | - | 0.10 |
| J | 0.047 | 0.127 | 0.207 |
| K | 2.60 | 2.80 | 3.00 |
| All Dimensions in mm | | | |