

MOLLY-M

~35° medium beam

SPECIFICATION:

Dimensions	Ø 69.8 mm
Height	23.6 mm
ROHS compliant	yes ⓘ




MATERIALS:

Component	Type	Material	Colour	Finish
MOLLY-M	Single lens	PMMA	clear	







ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
C15801_MOLLY-M	198	36	18	9.0
» Box size: 476 x 273 x 292 mm				



See also our general installation guide: www.ledil.com/installation_guide


OPTICAL RESULTS (MEASURED):

	<p>LED V11 HD Gen 8 FWHM / FWTM 33.0° / 52.0° Efficiency 90 % Peak intensity 2.4 cd/lm LEDs/each optic 1 Light colour White Required components: Bender Wirth: 633d 3Hook</p>		
	<p>LED Vero SE 13 FWHM / FWTM 36.0° / 54.0° Efficiency 90 % Peak intensity 2.1 cd/lm LEDs/each optic 1 Light colour White Required components: C16402_CLAMP-VEROSE-13-18</p>		
	<p>LED Vero SE 18 FWHM / FWTM 40.0° / 62.0° Efficiency 89 % Peak intensity 1.7 cd/lm LEDs/each optic 1 Light colour White Required components: C16402_CLAMP-VEROSE-13-18</p>		
	<p>LED Vesta TW 15mm DP FWHM / FWTM 38.0° / 58.0° Efficiency 90 % Peak intensity 1.9 cd/lm LEDs/each optic 1 Light colour Tunable White Required components: C13658_CLAMP-VERO13-18 Bender Wirth: 482 Typ L2</p>		

OPTICAL RESULTS (MEASURED):




LED Vesta TW 18mm (31W) DP
 FWHM / FWTM 40.0° / 61.0°
 Efficiency 88 %
 Peak intensity 1.7 cd/lm
 LEDs/each optic 1
 Light colour Tunable White
 Required components:
 C13584_CLAMP-VERO29
 Bender Wirth: 483 Typ L3





CITIZEN

LED CLL03x/CLU03x
 FWHM / FWTM 36.0° / 55.0°
 Efficiency 89 %
 Peak intensity 2.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 Bender Wirth: 433 Typ L1




CITIZEN

LED LCN-C02B (Tunable White)
 FWHM / FWTM 35.0° / 53.0°
 Efficiency 89 %
 Peak intensity 2.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C13658_CLAMP-VERO13-18
 Bender Wirth: 481 Typ L2



CREE LEDs



LED CMA1840
 FWHM / FWTM 37.0° / 56.0°
 Efficiency 91 %
 Peak intensity 2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14123_CLAMP-CXA15-18





OPTICAL RESULTS (MEASURED):





LED CMA2550
FWHM / FWTM 42.0° / 62.0°
Efficiency 89 %
Peak intensity 1.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C14036_CLAMP_CXA25-30





LED CMA3090
FWHM / FWTM 45.0° / 68.0°
Efficiency 88 %
Peak intensity 1.4 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C14036_CLAMP_CXA25-30




LED CMT14xx
FWHM / FWTM 33.0° / 50.0°
Efficiency 90 %
Peak intensity 2.5 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13658_CLAMP-VERO13-18
Bender Wirth: 434 Typ L1




LED CMT19xx
FWHM / FWTM 36.0° / 55.0°
Efficiency 90 %
Peak intensity 2.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
C13658_CLAMP-VERO13-18
Bender Wirth: 477 Typ L1



OPTICAL RESULTS (MEASURED):





OPTICAL RESULTS (MEASURED):




OPTICAL RESULTS (MEASURED):




LED CTM-22 (Tunable White)
 FWHM / FWTM 42.0° / 64.0°
 Efficiency 87 %
 Peak intensity 1.5 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C13584_CLAMP-VERO29
 Bender Wirth: 494 Typ L3




LED NVCWJ024Z-V1MT: COB J-Type Tunable White
 FWHM / FWTM 33.0° / 51.0°
 Efficiency 89 %
 Peak intensity 2.4 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C13658_CLAMP-VERO13-18
 Bender Wirth: 498 Typ L2



LED PrevalLED Core G7 L15 H1
 FWHM / FWTM 35.0° / 55.0°
 Efficiency 90 %
 Peak intensity 2.1 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C16685_CLAMP-PRV-A



LED Fortimo SLM L13 CoB
 FWHM / FWTM 35.0° / 53.0°
 Efficiency 89 %
 Peak intensity 2.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 TE Connectivity: 2213130-2 + OPTIC CLIP Z50 TYPE1 2213194-1





OPTICAL RESULTS (MEASURED):

PHILIPS

LED	Fortimo SLM L15 + SLM holder
FWHM / FWTM	34.0° / 53.0°
Efficiency	89 %
Peak intensity	2.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

TE Connectivity: OPTIC CLIP Z50 TYPE1 2213194-1




PHILIPS

LED	Fortimo SLM L15 CoB
FWHM / FWTM	36.0° / 54.0°
Efficiency	88 %
Peak intensity	2.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

TE Connectivity: 2213130-2 + OPTIC CLIP Z50 TYPE1 2213194-1




SAMSUNG

LED	LC035T (Tunable white)
FWHM / FWTM	43.0° / 67.0°
Efficiency	88 %
Peak intensity	1.4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

C13584_CLAMP-VERO29
Bender Wirth: 502 Typ L3





XICATO

LED	XTM - 19mm LES
FWHM / FWTM	39.0° / 60.0°
Efficiency	90 %
Peak intensity	1.8 cd/lm
LEDs/each optic	1
Light colour	White

Required components:


C16491_XTM-ADAPTER-50-A




OPTICAL RESULTS (SIMULATED):



LED V9 HD Gen7
FWHM / FWTM 32.0° / 44.0°
Efficiency 90 %
Peak intensity 3.3 cd/lm
LEDs/each optic 1
Light colour White
Required components:
 C13658_CLAMP-VERO13-18
 Bender Wirth: 496 Typ L1




LED VERO13
FWHM / FWTM 32.0° / 46.0°
Efficiency 91 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
 C13658_CLAMP-VERO13-18




CITIZEN

LED CLL02x/CLU02x (LES10)
FWHM / FWTM 30.0° / 42.0°
Efficiency 89 %
Peak intensity 3.6 cd/lm
LEDs/each optic 1
Light colour White
Required components:
 Bender Wirth: 434 Typ L1




LED CXA/B 1816 & CXA/B 1820 & CXA 1850
FWHM / FWTM 33.0° / 47.0°
Efficiency 90 %
Peak intensity 3.1 cd/lm
LEDs/each optic 1
Light colour White
Required components:
 C14123_CLAMP-CXA15-18




OPTICAL RESULTS (SIMULATED):



LED CXA/B 25xx
 FWHM / FWTM 36.0° / 50.0°
 Efficiency 88 %
 Peak intensity 2.2 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C14036_CLAMP_CXA25-30



LED CTM-18 (Tunable White)
 FWHM / FWTM 34.0° / 47.0°
 Efficiency 80 %
 Peak intensity 2.3 cd/lm
 LEDs/each optic 1
 Light colour White
 Required components:
 C13658_CLAMP-VERO13-18



GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

**Ledil Optics Technology
(Shenzhen) Co., Ltd.**
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

**Local sales and technical
support**
www.ledil.com/
where_to_buy

Shipping locations
Salo, Finland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy