


**DESIGNED AND DIMENSIONED IN INCHES [MILLIMETERS]**  
**ALL DIMENSIONS REFERENCE EXCEPT AS SHOWN**


DO NOT  
SCALE FROM  
THIS PRINT



**FIG 1**  
**240-J-P-EP-ST-CM-X-X SHOWN**

## NOTES:

1. RECOMMENDED MOUNTING TORQUE 0.5~0.8 INCH-POUNDS.
2. THIS IS A GENERAL FOOTPRINT AND IS NOT OPTIMIZED FOR ELECTRICAL PERFORMANCE, CONTACT SIG@SAMTEC.COM FOR ASSISTANCE WITH ELECTRICAL LAYOUT.



240-J-P-EP-ST-CM-X-X

SERIES  
240: 2.40MMGENDER  
-J: JACKTYPE  
-P: PCB

FINISH

-EP: 50 $\mu$ " EXTRA HEAVY GOLD  
CENTER CONTACT, PASSIVATED  
OUTER CONTACT

PACKAGING

-BLANK: INDIVIDUALLY BAGGED  
-B: FULL TRAY (QTY = 100 MIN OR MULTIPLES OF 100)

OPTION


- 1: OPTION 1 (WITHOUT SCREWS)
- 2: OPTION 2 (FOR PCB THICKNESS .016" TO .125")
- 3: OPTION 3 (FOR PCB THICKNESS .069" TO .178")

TERMINATION

-CM: COMPRESSION MOUNT STRIPLINE

ORIENTATION

-ST: STRAIGHT



<b>PROPRIETARY NOTE</b> <small>THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.</small>	
MATERIAL:	DO NOT SCALE DRAWING SHEET SCALE: 6:1
BODY, BUSHING & SCREW: STAINLESS STEEL SOCKET: COPPER ALLOY	DESCRIPTION: 2.40MM ST JACK FOR COMPRESSION MOUNT STRIPLINE
DWG. NO.	240-J-P-EP-ST-CM-X-X
BY: SHERRY W	7/10/2019 SHEET 1 OF 1

**Samtec**

520 PARK EAST BLVD, NEW ALBANY, IN 47150  
 PHONE: 812-944-6733 FAX: 812-948-5047

e-Mail: info@SAMTEC.com Code: 55322