

IRENE-IR-4

~65° + 65° rectangular beam

SPECIFICATION:

Dimensions Ø 21.6 mm
Height 14.3 mm
Fastening glue, pin
ROHS compliant yes 1



MATERIALS:

ComponentTypeMaterialColourFinishIRENE-4Multi-lensPMMAclearIRENE-HLDHolderPCwhite

ORDERING INFORMATION:


 Component
 Qty in box
 MOQ
 MPQ
 Box weight (kg)

 CP13069_IRENE-IR-4
 Multi-lens
 1792
 336
 112
 10.6

 » Box size: 480 x 280 x 300 mm
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6
 10.6</t



PRODUCT DATASHEET CP13069_IRENE-IR-4



See also our general installation guide: www.ledil.com/installation_guide



OPTICAL RESULTS (MEASURED):

OSRAM

LED SFH 4715S FWHM / FWTM 67.0° Efficiency % LEDs/each optic Light colour White Required components:

OSRAM Opto Semiconductors

LED SFH 4725S FWHM / FWTM 68.0° / 96.0°

Efficiency % LEDs/each optic 1 White Light colour Required components:




MUMILEDS

LED LUXEON IR 2720 FWHM / FWTM 74.0 + 66.0° / 97.0 + 92.0°

Efficiency 93 % LEDs/each optic 1 Light colour IR

Required components:



MILEDS

LED LUXEON IR Compact FWHM / FWTM 72.0 + 62.0° / 89.0 + 83.0°

Efficiency 79 %
LEDs/each optic 1
Light colour White


Required components:

OSRAM Opto Semiconductors


LED SFH 4714A

FWHM / FWTM 78.0 + 66.0° / 102.0 + 91.0°

Efficiency 71 %
LEDs/each optic 1
Light colour IR
Required components:









OSRAM

LED SFH 4725AS

FWHM / FWTM 70.0 + 62.0° / 91.0 + 85.0°

Efficiency 92 % LEDs/each optic 1
Light colour IR
Required components:







OSRAM

LED SFH 4770S

FWHM / FWTM 63.0 + 53.0° / 89.0 + 82.0°

Efficiency 92 % LEDs/each optic 1 Light colour White


Required components:

STANLEY


LED FWR1107MS

FWHM / FWTM 66.0 + 59.0° / 91.0 + 84.0°

Efficiency 93 % LEDs/each optic 1 Light colour IR Required components:







STANLEY


LED FWR1108MS

FWHM / FWTM 75.0 + 67.0° / 97.0 + 91.0°

Efficiency 92 %
LEDs/each optic 1
Light colour IR
Required components:








STANLEY

LED MFN1107MS
FWHM / FWTM 53.0° / 84.0°
Efficiency 91 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour IR

Light colour
Required components:





STANLEY


LED MFN1108MS

FWHM / FWTM 81.0° / 99.0° Efficiency 91 %

Peak intensity 0.8 cd/lm

LEDs/each optic 1 Light colour IR

Required components:



STANLEY

LED MGN1107MS


FWHM / FWTM 53.0° / 84.0°

Efficiency 91 %

Peak intensity 1.2 cd/lm

LEDs/each optic 1 Light colour IR

Required components:



STANLEY

LED MGN1108MS


FWHM / FWTM 81.0° / 99.0°

Efficiency 91 %

Peak intensity 0.8 cd/lm

LEDs/each optic 1
Light colour IR

Required components:




STANLEY

LED MJN1107MS


FWHM / FWTM 69.0 + 61.0° / 91.0 + 88.0°

Efficiency 92 %
LEDs/each optic 1
Light colour IR

Required components:









PRODUCT DATASHEET CP13069_IRENE-IR-4

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 13 FI-24240 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Salo, Finland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy