

Europe: +49 / 7731 8399 0

ISA: +1 / 508 295 0771

Asia: +852 / 2955 1682

| Email: info@standexmeder.com

| Email: salesusa@standexmeder.com

| Email: salesasia@standexmeder.com

Item No.:


9171800022

Item:

MK17-B-2

Version:

17



Modifications in the sense of technical progress are reserved

Designed at: 03.11.08 Designed by: THAUKE Approval at: 05.11.08 Approval by: JHEYDER
Last Change at: 29.12.14 Last Change by: AAI Approval at: 28.01.15 Approval by: AWEBER



Europe: +49 / 7731 8399 0

USA: +1 / 508 295 0771

Asia: +852 / 2955 1682

| Email: info@standexmeder.com

| Email: salesusa@standexmeder.com

| Email: salesasia@standexmeder.com

Item No.:

9171800022

Item:

MK17-B-2

Version: 17

Magnetic properties	Conditions	Min	Тур	Max	Unit	
Pull-In	at 20°C	28		48		
Test equipment		KMS-11				
Pull-In in milliTesla (modified conta	MS150 - phys. caused tolerance +/- 0,1mT	1,63		2,4	mT	
Test equipment		MS-150				

Contact data 80	Conditions	Min	Тур	Max	Unit		
Contact-material			Rhodium				
Contact-rating	Any DC combination of V & A not to exceed their individual max.'s			10	W		
Switching voltage	DC or Peak AC			100	V		
Carry current	DC or Peak AC			0,5	Α		
Switching current	DC or Peak AC			0,5	Α		
Contact resistance static	Measured with 40% overdrive Start Value			250	mOhm		
Breakdown voltage	according to IEC 255-5	150			VDC		

Special Product Data	Conditions	Min	Тур	Max	Unit	
Housing material		epoxy resin				
Material		EN 60335-1 conform				

Environmental data	Conditions	Min	Тур	Max	Unit
Shock	1/2 sine wave duration 11ms			30	g
Vibration	from 10 - 2000 Hz			20	g
Operating temperature		-40		130	°C
Storage temperature		-50		130	°C
Soldering Temperature Tsold	Reflow acc.IPC/JEDEC J-STD-020D.1			260	°C
Washability		fully sealed			

General data	Conditions	Min	Тур	Max	Unit	
Component marking	general descripton	B YM				

Modifications in the sense of technical progress are reserved

Designed at: 03.11.08 Designed by: THAUKE Approval at: 05.11.08 Approval by: JHEYDER

Last Change at: 29.12.14 Last Change by: AAI Approval at: 28.01.15 Approval by: AWEBER