

SACC-P12FS-5CT-CM SH - Connector



1021817

<https://www.phoenixcontact.com/us/products/1021817>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 5-position, shielded, Socket straight M12 Push-Pull, coding: A, Crimp connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4.5 mm ... 7.5 mm, without crimp contacts

Your advantages

- Plug and Produce: convenient and secure connection, thanks to the manufacturer-independent locking system
- Extremely compact, thanks to the small wiring space and high contact density
- Clear feedback: the connector springs back when not snapped into place correctly
- Safely shielded: reliable shield connection even under extreme mechanical strain
- Robust connection: suitable for railway applications with high shock and vibration loads

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1021817 |
| Packing unit | 1 pc |
| Sales key | BF34 |
| Product key | BF2CJA |
| GTIN | 4055626514666 |
| Weight per piece (including packing) | 28.8 g |
| Weight per piece (excluding packing) | 22.22 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-P12FS-5CT-CM SH - Connector



1021817

<https://www.phoenixcontact.com/us/products/1021817>

Technical data

Notes

| | |
|---------|--|
| General | NOTE: Observe the permissible bending radii when laying conductors, since the degree of protection may be put in jeopardy if the bending forces are too high. Alleviate mechanical loads upstream of the connector, e.g. by using cable ties. |
|---------|--|

Mounting

| | |
|-----------------------|--|
| Assembly instructions | Contacts can be clipped in place and unclipped without tools |
| Connection method | Crimp connection |


Product properties

| | |
|----------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Sensor type | Universal |
| Number of positions | 5 |
| No. of cable outlets | 1 |
| Shielded | yes |
| Coding | A |
| Cable outlet | straight |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Dimensions

| | |
|--------------------------|--|
| Dimensional drawing |  |
| Wrench size, union nut | 15 mm |
| Wrench size, counter nut | 14 mm |

External dimensions

| | |
|------------------|-------------------|
| Outside diameter | 4.5 mm ... 7.5 mm |
|------------------|-------------------|

Housing

| | |
|------------------|-------|
| Diameter housing | 22 mm |
|------------------|-------|

Material specifications

| | |
|--|------------------------------|
| Flammability rating according to UL 94 | V0 |
| Seal material | NBR |
| Material of grip body | Zinc die-cast, nickel-plated |

SACC-P12FS-5CT-CM SH - Connector



1021817

<https://www.phoenixcontact.com/us/products/1021817>

| | |
|-------------------------------|--|
| Contact carrier material | PA 6.6 |
| Material for screw connection | Zinc die-cast, nickel-plated |
| Standards/regulations | PA 6.6: Fire protection in rail vehicles - requirement sets R22, R23, R24, and R26 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |

Connection data

Conductor connection

| | |
|---|---|
| Connection method | Crimp connection |
| Connection cross section | 0.14 mm ² ... 1 mm ² (flexible) |
| Connection cross section AWG | 26 ... 18 (flexible) |
| Stripping length of the individual wire | 4 mm +0,5 mm |
| Tightening torque | 4 Nm (Pressure nut with coupling sleeve) |

Electrical properties

| | |
|--------------------------------|----------|
| Rated surge voltage | 1.5 kV |
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U _N | 60 V DC |
| | 48 V AC |
| Nominal current I _N | 4 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

Connector

Connection 1

| | |
|-------------------|-----------|
| Head design | Socket |
| Head cable outlet | straight |
| Head thread type | M12 |
| Head locking type | Push-Pull |
| Coding | A |

Cable/line

| | |
|---|--------------|
| Signal type/category | Universal |
| Stripping length of the individual wire | 4 mm +0,5 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|----------------------------------|
| Degree of protection | IP65 |
| Ambient temperature (operation) | -40 °C ... 85 °C (Plug / socket) |

Standards and regulations

SACC-P12FS-5CT-CM SH - Connector



1021817

<https://www.phoenixcontact.com/us/products/1021817>

Testing

| | |
|--------------------------|--|
| Standards/regulations | PA 6.6: Fire protection in rail vehicles - requirement sets R22, R23, R24, and R26 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |
| Note | In line with |
| Standard designation | Shock, vibration |
| Standards/specifications | EN 50155:2001 |

SACC-P12FS-5CT-CM SH - Connector




1021817

<https://www.phoenixcontact.com/us/products/1021817>


Drawings

Schematic diagram



M12 PUSH-PULL male pin assignment, 5-pos., socket-side view

Dimensional drawing




M12 PUSH-PULL female, straight, shielded

SACC-P12FS-5CT-CM SH - Connector

1021817

<https://www.phoenixcontact.com/us/products/1021817>

Functional drawing



Functional drawing

SACC-P12FS-5CT-CM SH - Connector



1021817

<https://www.phoenixcontact.com/us/products/1021817>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 8.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-P12FS-5CT-CM SH - Connector



1021817

<https://www.phoenixcontact.com/us/products/1021817>

Environmental product compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

SACC-P12FS-5CT-CM SH - Connector



1021817

<https://www.phoenixcontact.com/us/products/1021817>

Mandatory accessories

CC1,0-TS-0,34F AU - Crimp contact

1064041

<https://www.phoenixcontact.com/us/products/1064041>



Crimp contact, contact diameter: 1 mm, turned, Socket, contact material: CuZn, contact surface: Ni/Au, connection cross section: 0.14 mm² ... 0.34 mm², AWG 26 ... 22

CC1,0-TS-1,00F AU - Crimp contact

1423646

<https://www.phoenixcontact.com/us/products/1423646>



Crimp contact, contact diameter: 1 mm, turned, Socket, contact material: CuZn, contact surface: Ni/Au, connection cross section: 0.34 mm² ... 1 mm², AWG 22 ... 18

Accessories

SACC-P12FS-5CT-CM SH - Connector



1021817

<https://www.phoenixcontact.com/us/products/1021817>

CRIMPFOX-TC MP - Crimping pliers with digital display

1212510

<https://www.phoenixcontact.com/us/products/1212510>



Crimping pliers, for turned contacts, universal cross section setting, up to a maximum of 2.5 mm², digital display with 0.01 mm increments, pressure lock can be unlocked, including positioning tool

MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/us/products/1212489>



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

SACC-P12FS-5CT-CM SH - Connector



1021817

<https://www.phoenixcontact.com/us/products/1021817>

WIREFOX-D 13 - Stripping tool

1212162

<https://www.phoenixcontact.com/us/products/1212162>



Stripping tool, for stripping installation lines of \varnothing 8 - 13 mm , e.g. NYM 3 x 1.5 mm² to 5 x 2.5 mm², single line stripping 0.2 mm² - 4 mm² , with longitudinal cut blade and sliding knife

WIREFOX SAC - Stripping tool

1212623

<https://www.phoenixcontact.com/us/products/1212623>



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from \varnothing of 4.4 to 7 mm, any stripping length

SACC-P12FS-5CT-CM SH - Connector

1021817

<https://www.phoenixcontact.com/us/products/1021817>



VS-CABLE-STRIP-VARIO - Stripping tool

1657407

<https://www.phoenixcontact.com/us/products/1657407>

Stripping tool, for the multi-level stripping of shielded cables



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com